



## Part No: 3013W3SAM99A30X

### Product Description

- D-SUB Combination Standard
- 13W3 [o.....oo]
- Socket
- Solder cup
- Threaded Insert
- UNC 4-40

Inquiry

| General Data                            | Technical Data  | Material Data | Standards | Downloads |
|-----------------------------------------|-----------------|---------------|-----------|-----------|
| Dielectric with standing voltage signal | 1000 V          |               |           |           |
| min. working temperature                | -55° C          |               |           |           |
| Quality class                           | Quality class 3 |               |           |           |
| Mating cycles                           | 50              |               |           |           |
| IP rating                               | IP 20           |               |           |           |
| Insertion force                         | 55 N            |               |           |           |
| Extraction force                        | 23 N            |               |           |           |
| Contact resistance standard             | 8 mOhm          |               |           |           |