



Part No: 301A10959X

Product Description

- D-SUB Standard
- 25-pos.
- Plug
- Solder Pin angled .318" stamped Contacts
- Plastic bracket
- Quality class 3
- UNC 4-40

[Inquiry](#)

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage signal		1000 V		
Quality class		Quality class 3		
Mating cycles		50		
IP rating		IP 20		
Insertion force		<83 N		
min. working temperature		-55° C		
max. working temperature		+125° C		