

Image gallery

3D view



Part No: 3036W4PAR99F20X

Product Description

- D-SUB Combination Standard
- 36W4 [0.....000]
- Plug
- Solder pin straight
- Threaded rear spacer
- UNC 4-40

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
min. working temperature	-55° C
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	137 N
Extraction force	34 N
Contact resistance standard	8 mOhm