


Image gallery

3D view



Part No: 321WA4SAR99E40X

Product Description

- D-SUB Combination Standard
- 21WA4 [○○.....○○]
- Socket
- Solder pin straight
- Threaded rear spacer
- UNC 4-40

Inquiry

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
min. working temperature	-55° C
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	86 N
Extraction force	31 N
Contact resistance standard	8 mOhm