



Part No: 3F3SSA22S43A20X

Product Description

- Filter Combination D-SUB
- 3W3 [000]
- Socket
- C-Filter
- 47 nF
- Threaded Insert

Inquiry

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage power		707 V DC		
Capacitor value power contact		47 nF		
Power contact cross section		AWG 10- 12		
Working voltage power		100 V DC		
Quality class		Quality class 3		
Mating cycles		50		
IP rating		IP 20		
Current rating power		30 A		
Insertion force		21 N		
Extraction force		21 N		
min. working temperature		-55° C		
max. working temperature		+125° C		
Filter type		C		