



3D view

Part No: 6HDD15SAM99B20X

Product Description

- IP67 D-SUB High Density
- 15-pos.
- Socket
- Solder cup

[Inquiry](#)

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage signal	1000 V			
Quality class	Quality class 3			
Mating cycles	50			
IP rating	IP67			
Insertion force	50 N			
Extraction force	50 N			
Contact resistance standard	10 mOhm			
min. working temperature	-25° C			
max. working temperature	+105° C			