


Image gallery

3D view



Part No: 8F8SPA12S43A30X

Product Description

- Filter Combination D-SUB
- 8WB [oooooooo]
- Plug
- C-Filter
- 10 nF
- Threaded Insert

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage power	707 V DC
Capacitor value power contact	10 nF
Power contact cross section	AWG 10- 12
Working voltage power	100 V DC
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Current rating power	30 A
Insertion force	56 N
Extraction force	56 N
min. working temperature	-55° C
max. working temperature	+125° C
Filter type	C