

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0190730218
Status: Active
Overview: Solderless Terminals
Description: Avikrimp™ Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 6 (M3.5), Length 26.59mm, Mylar Tape Carrier

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E32244


General
Product Family Ring and Spade Terminals
Series 19073
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Solderless Terminals
Product Name Avikrimp™
Type Ring
UPC 800753077546

Physical
Barrel Type Closed
Flammability 94V-2
Insulation Nylon (PA)
Material - Plating Mating Tin
Net Weight 2.202/g
Packaging Type Adhesive Tape on Reel
Stud Size 6 (M3.5)
Wire Insulation Diameter 5.72mm max.
Wire Size AWG 10, 12
Wire Size mm² 3.30-5.00

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number C-836-06T

Reference - Drawing Numbers
Product Specification PS-19902-011-001, PS-19902-015-001
Sales Drawing SD-19073-008



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Contained Per - ED/30/2017 (7 July 2017) 2,4-Di-tert-butyl-6-(5- chlorobenzotriazol-2- yl)p	China RoHS
---	-------------------

Halogen-Free
Status
Low-Halogen
Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
19073 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION