

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5055650201

Status:


Active

Overview:

Micro-Lock Plus Wire-to-Board Connector System

Description:

1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Single Row, Positive Lock, 2 Circuits, Black



Documents:	
Drawing (PDF)	Application Specification AS-505565-001-001 (PDF)
3D Model	Packaging Specification 5055659200-200 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5055650000-000 (PDF)	Product Literature (PDF)
Product Specification 5055650002-000 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	505565
Application	Signal, Wire-to-Board
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Literature Order No	987651-4888
Product Name	Micro-Lock Plus
UPC	889056502900
Physical	
Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	67.955/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-505565-001-001
Packaging Specification	5055659200-200
Product Specification	5055650000-000, 5055650002-000
Sales Drawing	5055650002-SD-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
505565 Series
Mates With
Micro-Lock Plus Vertical Header 505568
 Micro-Lock Plus Right Angle Header 505567
Use With
Micro-Lock Plus Terminal 505431

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION