



Part Number : [1110751008](#)
Product Description : Mini-SAS HD-to-Mini-SAS HD
3.0, 4X Cable Assembly with External Shielding, 8.0m
Length, 24 AWG
Series Number : 111075
Status : Not Recommended For New Design
Product Category : High-Speed I/O Cable
Assemblies
Engineering Part Number : 111075-10085

Documents and Resources

Drawings

[1110751008_sd.pdf](#)
[PK-111075-1007-001.pdf](#)

Specifications

[1110750001-000.pdf](#)
[2040400001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Contains bis(2-ethylhexyl) tetrabromophthalate covering any of the individual isomers and/or combinations thereof per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Relevant

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	High-Speed I/O Cable Assemblies
Series	111075
Description	Mini-SAS HD-to-Mini-SAS HD 3.0, 4X Cable Assembly with External Shielding, 8.0m Length, 24 AWG
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini SAS-to-Mini SAS
Product Name	Mini-SAS
Type	Pluggable
UPC	887191226859

Agency

UL	E72548
----	--------

Electrical

Data Rate	12.0 Gbps
Impedance	100Ω

Physical

Cable Bundling	None
Cable Length	8.0m

Circuits (Loaded)	36
Circuits (maximum)	36
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Zinc Alloy
Material - Plating Mating	Gold
Net Weight	1530.117/g
Packaging Type	Bag
Release Style	Pull Tab
Single Ended	No
Waterproof / Dustproof	No
Wire/Cable Type	Parallel Pair
Wire Size (AWG)	24