



Part Number : [135130001](#)

Product Description : Button RFID Tag, 24.9mm Read Range, 22.00mm Diameter Footprint, For Metal Surfaces, Screw or Adhesive Attachment

Series Number : 13513

Status : Active

Product Category : Asset Tracking

Documents and Resources

Drawings

[135130001_sd.pdf](#)

Specifications

[135130001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Asset Tracking
Series	13513
Description	Button RFID Tag, 24.9mm Read Range, 22.00mm Diameter Footprint, For Metal Surfaces, Screw or Adhesive Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Metal Surfaces
UPC	196823154119

Electrical

Frequency	13.56 MHz
-----------	-----------

Physical

Dimensions	22.00mm dia x 3.00mm Thickness
Mounting Style	Adhesive, Screws
Outer Diameter	22.00mm
Packaging Type	Bag
Read Range	24.9mm
Thickness	3.00mm