



Part Number : [1510340013](#)
Product Description : 11.00mm Pitch EXTreme
Guardian Power Receptacle Assembly, PBT, 3 Circuits
Series Number : 151034
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

[1510340013_sd.pdf](#)
[PK-151034-0001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[PS-151053-0000-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	151034
Description	11.00mm Pitch EXTreme Guardian Power Receptacle Assembly, PBT, 3 Circuits
Application	Power, Wire-to-Board
Product Name	EXTreme Guardian
UPC	889056063425

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	PBT

Net Weight	17.728/g
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	11.00mm
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme Guardian Power Plugs	<u>151035</u>
EXTreme Guardian Power Vertical Plugs	<u>151053</u>

Use with Part(s)

Description	Part Number
11.00mm Pitch EXTreme Guardian Receptacle TPA Clip, 3 Circuits	<u>1510760013</u>
EXTreme Guardian Female High Power Terminals	<u>46819</u>