



Part Number : [732309391](#)


Product Description : MCX Right-Angle Plug to MCX Right-Angle Plug on .086" Semi Rigid Cable, 152.40mm Length, 50 Ohms

Series Number : 73230

Status : Active

Product Category : RF Cable Assemblies

Engineering Part Number : 25P203C25P2-006



Documents and Resources

Drawings

[732309391_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF Cable Assemblies
Series	73230
Description	MCX Right-Angle Plug to MCX Right-Angle Plug on .086" Semi Rigid Cable, 152.40mm Length, 50 Ohms
Application	RF
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MCX-to-MCX
Product Name	MCX
Type	RF Cable Assembly
UPC	191128303309

Electrical

Frequency	6 GHz
Impedance	50Ω

Physical

Cable Length	152.40mm
Gender	Plug/Plug
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Resin	PTFE
Net Weight	0.001/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	RG-405 (.086" Semi-Rigid Cable)

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCX Plugs and Jacks	<u>73366</u>

This document was generated on Feb 27, 2026