




**Part Number :** [982671100](#)

**Product Description :** 1.00mm Pitch Premo-Flex FFC  
Jumper, Opposite Side Contacts (Type D), 76.00mm  
Cable Length, Tin (Sn) Plating, 39 Circuits

**Series Number :** 98267

**Status :** Active

**Product Category :** Flat-Flexible Cable (FFC)



---

## Documents and Resources

### Drawings

[982671100 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-98267-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|              |                                                                                                                          |
|--------------|--------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                   |
| Category     | Flat-Flexible Cable (FFC)                                                                                                |
| Series       | 98267                                                                                                                    |
| Description  | 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 76.00mm Cable Length, Tin (Sn) Plating, 39 Circuits |
| Comments     | Contacts on opposite sides, Type D                                                                                       |
| Product Name | Premo-Flex FFC Jumper                                                                                                    |
| UPC          | 800756947433                                                                                                             |

### Electrical

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.2A   |
| Voltage - Maximum             | 60V AC |

### Physical

|                               |                   |
|-------------------------------|-------------------|
| Cable Length                  | 76.00mm           |
| Circuits (Loaded)             | 39                |
| Contact Layout Type           | D (opposite side) |
| Design Feature                | Extra-Flexible    |
| Material - Plating Mating     | Tin               |
| Packaging Type                | Bag               |
| Pitch - Mating Interface      | 1.00mm            |
| Temperature Range - Operating | -40° to +105°C    |
| Termination Style             | FFC Connector     |
| Wire/Cable Type               | Flat Flex Cable   |
| Wire Size (AWG)               | N/A               |

