

HC-DCC06-HHFD-1TGESM32-PLBK - Housing



1551459

<https://www.phoenixcontact.com/nl/products/1551459>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing DCC06, for double locking latch, material: PA 6, cable outlets: 1, straight, 1x M32, height: 139.9 mm, cable gland: with, Power supply in data centers, with extra-strong strain relief

Your advantages

- Lower costs than metal version
- Low weight

Commercial data

Item number	1551459
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF7APS
Product key	AF7APS
GTIN	4067923028616
Weight per piece (including packing)	138,8 g
Weight per piece (excluding packing)	129,5 g
Customs tariff number	85389099
Country of origin	PL

HC-DCC06-HHFD-1TGESM32-PLBK - Housing



1551459

<https://www.phoenixcontact.com/nl/products/1551459>

Technical data


Notes

General	Connectors may be operated only when there is no load/voltage.
---------	--

Product properties

Housing type	Sleeve housing
Series	HC-DCC
Application	Power supply in data centers
No. of cable outlets	1
Type of the screw connection	1x M32
Shielded	no
Cable outlet	straight
Pg screw connection	with

Dimensions

Dimensional drawing	
Width	53.8 mm
Height	139.9 mm
Length	60.5 mm
Clamping range of the strain relief clip	11.00 mm ... 21.00 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Seal material	NBR
Housing material	PA 6

Mechanical properties

Mechanical data

Type of the screw connection	1x M32
Locking type	Pin

Cable/line

External cable diameter	11 mm ... 21 mm
-------------------------	-----------------

Connection data

External cable diameter	11 mm ... 21 mm
-------------------------	-----------------

HC-DCC06-HHFD-1TGESM32-PLBK - Housing



1551459

<https://www.phoenixcontact.com/nl/products/1551459>

Tightening torque	7.5 Nm ... 7.5 Nm
Tightening torque contact carrier	1.2 Nm

Mounting

Assembly note	Connectors may only be actuated when there is no load/voltage.
---------------	--

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 125 °C

HC-DCC06-HHFD-1TGESM32-PLBK - Housing


1551459

<https://www.phoenixcontact.com/nl/products/1551459>



Drawings

Dimensional drawing



Dimensional drawing

HC-DCC06-HHFD-1TGESM32-PLBK - Housing



1551459

<https://www.phoenixcontact.com/nl/products/1551459>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-DCC06-HHFD-1TGESM32-PLBK - Housing



1551459

<https://www.phoenixcontact.com/nl/products/1551459>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl