



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'BSV10X-X'

Your search criteria matched only one product, shown below

BSV10X-X



- Expanded wire entry designed to accommodate wire with a larger insulation thickness
- Designed to splice two solid or stranded wires together to repair or lengthen wires
- Brazed seam protects terminal barrel from splitting during the crimp process
- Internal wire stop assures proper length of insertion into terminal barrel
- UL Flammability UL 94V -0, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600 V per UL 486

	Part Number	BSV10X-X
	RoHS Compliancy Status	Compliant
	Part Description	Butt Splice, 12– 10 AWG, vinyl insulated.
	Product Type	Splices
	CSA Certified	Yes
	UL Listed	Yes
	Length (In.)	1.17
	Length (mm)	29.7
	Angle	straight
	CE Compliant	No
	CE Marking	No
	Max. Ins.	.260
	Panduit Color Code	Yellow
	Pricing Description	Butt Splice, vinyl insulated, 12- 10 AWG
	Tool	CT-100A, CT-600-A, CT-1550, CT-1551, CT-2500
	Wire Range	12 – 10 AWG
	Wire Range (mm ²)	2.5 – 6.0
	Min. Order UOM	PC
	Min. Order Qty.	100
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.