

Search within category

GO

BUY NOW

DESIGN / INSTALL



STP28X4MBL

Category 6A Performance, 28AWG, F/UTP Patch Cord, CM/LSZH, Black, 4m.

Specs

Packaging Details

Documents

★ Add to Favorites

Add to BOM

Performance Level	Category 6A/Class EA
Cable Color	Black
Length (ft.)	13.12
Length (m)	4
Flammability Rating	CM/LSZH
Termination End 1	Modular Plug
Termination End 2	Modular Plug
Standards	PoE, PoE+
Wiring Scheme	T568B
CE Compliant	Yes
Nominal Cable O.D. (In.)	0.185
Nominal Cable O.D. (mm)	4.7
Operating Temperature	14°F to 140°F (-10°C to 60°C)
Storage Temperature	-40°F to 158°F (-40°C to 70°C)
UL5A Listed	No
Cable Type	F/UTP
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000