




+ WIRE AND CABLE
MULTICORE CABLE



✓ Active

TE CONNECTIVITY (TE)
55FB1511-20-7L-0
[Raychem](#) | [RC](#) , [SP](#)

55FB1511-20-7L-0
TE Internal Number: 871895-000
Alias ID: 1196785-8

[EU RoHS Compliant](#)
[EU ELV Compliant](#)
Cable Type Spec 55F
Overall Outside Diameter (in) .091
Voltage Rating (V) 600
Shielded Yes
Shield Material Tin-Plated Copper

↓ **PRODUCT DRAWING**
[English](#)

DOCUMENTATION

Product Drawings

ONE CONDUCTOR CABLE, SHIELDED, JACKETED, FILTER LINE - ELECTROLOSS
PDF
English

Product Specifications

Product Specification

Cable, Electric, Filter Line
PDF
English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Cable Type** Spec 55F
- Shielded** Yes
- Cable Style** Primary
- Product Type** Cable
- Product Classification** Cable - High Performance - Spec 44, 55 & RCW

Configuration Features

- Number of Conductors** 1

Electrical Characteristics

- Voltage Rating (V)** 600

Body Features

- Shield Material** Tin-Plated Copper
- Wire Color** Violet
- Conductor Material** Tin-Plated Copper

Dimensions

- Overall Outside Diameter (in)** .091
- Wire Size (AWG)** 20
- Wire Size (mm²)** .5176

Usage Conditions

- Operating Temperature Range (°C)** -65 – 150

Other

- Wire Source** United States
- Comment** Internal wire sizes 22-10 meets or exceeds all requirements of SAE AS85485/9, less identification., Product meets or exceeds all requirements of SAE AS85485/12 for 22-10 AWG, less identification.

PRODUCT COMPLIANCE

+

Statement of Compliance

- Statement of Compliance**
- PDF