STD/STB-TYPE SNAP-ON PRE-PRINTED WIRE & CABLE MARKERS

Identification

SNAP-ON PRE-PRINTED MARKERS FOR DIRECT APPLICATION ONTO WIRES & SMALL CABLES

TE Snap-On Markers are designed to offer flexibility with wire identification. Each marker is designed with a 'C' shape to firmly hold onto the wire accurately.

Markers can be accurately positioned onto the wire directly from the preloaded carrier wand. The chevron cut allows multiple markers alignment on the wire for easy identification. Manufactured from Zero Halogen polyoxymethylene STD markers are strong, durable and provide excellent chemical resistance.

SPEED-UP YOUR PROJECTS

- **Pre-Printed markers.** No Need for printers, ribbons and software. Markers are Pre-printed for easy and quick appplication.
- **Compact Design** 30 Markers are supplied on a Preloaded applicator between 120 cm & 140 cm in length.
- **Easy identification** Pre-printed letters, numbers and common signs. Colored markers are printed with international color coding (0-Black, 1-Brown etc.).

SECURED INSTALLATION

- **Visual control**: Snap-On marker can be applied directly to terminated or non terminated wire.
- **Quick and easy**: C shape marker profile allows easy fitting directly onto the wire and then holds.
- **Always perfect**: Chevron cut ensures marker alignment when using multiple markers together.

FOR ALL YOUR NEEDS

- **Strong and steady**: Zero Halogen polyoxymethylene giving strength, dimensional stability and low moisture absorption.
- **11 sizes available**: Marker sizes can cover wire diameters from 1 mm to 19 mm.
- **Extreme conditions**: Resist to temperature range from -40°C to 106°C. Resistant to key Industrial fluids. Self-extinguishing – UL94 HB Rated. RoHS and REACH compliance.



STD/STB-TYPE WIRE & CABLE MARKERS

STD/STB Markers are designed to offer flexibility when it comes to wire and cable identification. Used to identify wire and small cables, the 'C' shaped markers are designed to firmly hold onto the wire. Smaller size pre-printed markers (Size 01-15) are supplied on an applicator wand, applicator wands can also be purchased for larger sizes (Size 17-24). These help to apply the markers; their unique head allows each marker to expand before gripping the wire. Because of the application process, STD markers are ideal for post wire termination or installation when retrofitting is required.

STD colours are White & Yellow with a pre-printed black legend. STB are coloured markers with pre-printed black or white legend. All markers are supplied with a chevron cut the ensures alignment when using multiple marker together.

Manufactured from Zero Halogen polyoxymethylene STD markers are strong, durable and provide excellent chemical resistance.

Further questions? Consult your local TE Representative.

FEATURES AND BENEFITS

- Zero Halogen
- Self-extinguishing – UL94 HB Rated
- Resistant to key Industrial fluids including those used in Energy, oil refineries, aviation and military.

SPECIFICATIONS

- **Temperature rating:** operating range -40°C to 106°C (-40°F to 223°F)
- **Specifications and Approvals:** UL94 HB
- **For more information:**
  - Technical Datasheet: TTDS-094
  - Product specification Sheet: RW-2538.

SPECIFICATIONS

- Industrial
- Electrical Cabinet
- Oil & Gas.

ORDERING INFORMATION

STD - Color coded marker

LEGEND CODING	Sign					
Printed Marking	+	-	/	⏚	.	
Printed sign codification (legend)	PLUS	MINUS	SLASH	EARTH	DOT	BLANK

ORDERING DESCRIPTION SYSTEM



STB - Color coded marker

COLOR CODING	0	1	2	3	4	5	6	7	8	9

Only white & yellow are standard products.
Other colors on request.



STD/STB TYPE CROSS-REFERENCE TABLE FOR MARKERS & CORRESPONDING CABLES

PRODUCT/SIZE CODE STD - STB	Size	Cable diameter range Approx (mm)	Cable Size Approx (mm^2)	Pack Qty	Pack format
	01	1.00 - 1.40	0.78 - 1.50	300	10 applicatiors Pre-Loaded with 30 markers each
	02	1.40 - 1.80	1.50 - 2.54		
	03	1.90 - 2.65	2.83 - 5.47		
	05	2.30 - 3.00	4.15 - 7.06		
	06	2.60 - 3.50	5.30 - 9.62		
	09	3.25 - 4.50	8.24 - 15.90		
	12	4.50 - 6.00	15.90 - 28.27		
	15	5.80 - 8.50	26.42 - 56.74	50	Individual Markers
	17	8.50 - 11.5	56.74 - 103.8		Applicator available separately
	21	11.00 - 15.50	95.03 - 188.9		
	24	15.00 - 19.00	176.7 - 283.5		

STD MARKERS – SIZE 01

- Snap-On Markers
- Marker size '01'
- Marker Width: 2.3 mm
- Character Height: 0.3 mm
- For Cable Dia: 1.0 – 1.4 mm *(0.04 – 0.05 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	543032-000	STD01W-A	1768041-3	STD01Y-A	300	Pre-loaded
B	667794-000	STD01W-B	1768041-6	STD01Y-B		
C	490978-000	STD01W-C	1768041-9	STD01Y-C		
D	892212-000	STD01W-D	1-1768041-1	STD01Y-D		
E	306924-000	STD01W-E	1-1768041-4	STD01Y-E		
F	564572-000	STD01W-F	1-1768041-7	STD01Y-F		
G	476126-000	STD01W-G	1-1768041-9	STD01Y-G		
H	773592-000	STD01W-H	2-1768041-1	STD01Y-H		
I	744932-000	STD01W-I	2-1768041-3	STD01Y-I		
J	558694-000	STD01W-J	2-1768041-4	STD01Y-J		
K	300156-000	STD01W-K	2-1768041-5	STD01Y-K		
L	069822-000	STD01W-L	2-1768041-7	STD01Y-L		
M	797550-000	STD01W-M	2-1768041-9	STD01Y-M		
N	825954-000	STD01W-N	3-1768041-2	STD01Y-N		
O	380468-000	STD01W-0	9-1768040-2	STD01Y-0		
P	003470-000	STD01W-P	3-1768041-4	STD01Y-P		
Q	184430-000	STD01W-Q	3-1768041-6	STD01Y-Q		
R	127474-000	STD01W-R	3-1768041-7	STD01Y-R		
S	894140-000	STD01W-S	3-1768041-9	STD01Y-S		
T	381132-000	STD01W-T	4-1768041-1	STD01Y-T		
U	764856-000	STD01W-U	4-1768041-2	STD01Y-U		
V	117528-000	STD01W-V	4-1768041-3	STD01Y-V		
W	019350-000	STD01W-W	4-1768041-4	STD01Y-W		
X	165016-000	STD01W-X	4-1768041-5	STD01Y-X		
Y	098122-000	STD01W-Y	4-1768041-6	STD01Y-Y		
Z	030648-000	STD01W-Z	4-1768041-7	STD01Y-Z		
0	380468-000	STD01W-0	9-1768040-2	STD01Y-0		
1	036952-000	STD01W-1	9-1768040-3	STD01Y-1		
2	880874-000	STD01W-2	9-1768040-4	STD01Y-2		
3	261416-000	STD01W-3	9-1768040-5	STD01Y-3		
4	886014-000	STD01W-4	9-1768040-6	STD01Y-4		
5	472156-000	STD01W-5	9-1768040-7	STD01Y-5		
6	697328-000	STD01W-6	9-1768040-8	STD01Y-6		
7	115690-000	STD01W-7	9-1768040-9	STD01Y-7		
8	695082-000	STD01W-8	1768041-1	STD01Y-8		
9	524448-000	STD01W-9	1768041-2	STD01Y-9		
+	9-1768040-0	STD01W-PLUS	3-1768041-5	STD01Y-PLUS		
-	8-1768040-7	STD01W-MINUS	3-1768041-0	STD01Y-MINUS		
/	435160-000	STD01W-SLASH	4-1768041-0	STD01Y-SLASH		
⏚	8-1768040-0	STD01W-EARTH	1-1768041-5	STD01Y-EARTH		
.	7-1768040-9	STD01W-DOT	1-1768041-3	STD01Y-DOT		
	7-1768040-6	STD01W-BLANK				

		Coloured markers			
Printed Marking		TCPN	Part Description	Packaging size	Packaging type
0	Black	7-1768036-9	STB01-0-0	300	Pre-loaded
1	Brown	8-1768036-2	STB01-1-1		
2	Red	8-1768036-5	STB01-2-2		
3	Orange	8-1768036-8	STB01-3-3		
5	Green	9-1768036-3	STB01-5-5		
6	Blue	9-1768036-6	STB01-6-6		
7	Purple	9-1768036-9	STB01-7-7		
8	Gray	1768037-3	STB01-8-8		

STD MARKERS – SIZE 02

- Snap-On Markers
- Marker size '02'
- Marker Width: 2.4 mm
- Character Height: 1.4 mm
- For Cable Dia: 1.4 – 1.8 mm *(0.05 – 0.07 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	487180-000	STD02W-A	6-1768041-7	STD02Y-A	300	Pre-loaded
B	003324-000	STD02W-B	7-1768041-0	STD02Y-B		
C	055262-000	STD02W-C	7-1768041-3	STD02Y-C		
D	488834-000	STD02W-D	7-1768041-5	STD02Y-D		
E	397338-000	STD02W-E	7-1768041-8	STD02Y-E		
F	961776-000	STD02W-F	8-1768041-1	STD02Y-F		
G	145890-000	STD02W-G	8-1768041-3	STD02Y-G		
H	739622-000	STD02W-H	8-1768041-5	STD02Y-H		
I	340984-000	STD02W-I	8-1768041-7	STD02Y-I		
J	965732-000	STD02W-J	8-1768041-8	STD02Y-J		
K	167492-000	STD02W-K	8-1768041-9	STD02Y-K		
L	165426-000	STD02W-L	9-1768041-1	STD02Y-L		
M	701898-000	STD02W-M	9-1768041-3	STD02Y-M		
N	052350-000	STD02W-N	9-1768041-6	STD02Y-N		
O	103302-000	STD02W-0	6-1768041-6	STD02Y-0		
P	847560-000	STD02W-P	9-1768041-8	STD02Y-P		
Q	153592-000	STD02W-Q	1768042-1	STD02Y-Q		
R	703268-000	STD02W-R	1768042-2	STD02Y-R		
S	108520-000	STD02W-S	1768042-4	STD02Y-S		
T	424514-000	STD02W-T	1768042-6	STD02Y-T		
U	009222-000	STD02W-U	1768042-7	STD02Y-U		
V	421406-000	STD02W-V	1768042-8	STD02Y-V		
W	592248-000	STD02W-W	1768042-9	STD02Y-W		
X	141794-000	STD02W-X	1-1768042-0	STD02Y-X		
Y	273610-000	STD02W-Y	1-1768042-1	STD02Y-Y		
Z	471570-000	STD02W-Z	1-1768042-2	STD02Y-Z		
0	103302-000	STD02W-0	6-1768041-6	STD02Y-0		
1	819694-000	STD02W-1	557314-000	STD02Y-1		
2	341158-000	STD02W-2	983856-000	STD02Y-2		
3	313440-000	STD02W-3	709528-000	STD02Y-3		
4	028034-000	STD02W-4	365180-000	STD02Y-4		
5	939726-000	STD02W-5	996838-000	STD02Y-5		
6	996948-000	STD02W-6	859984-000	STD02Y-6		
7	147282-000	STD02W-7	972648-000	STD02Y-7		
8	318610-000	STD02W-8	379708-000	STD02Y-8		
9	479820-000	STD02W-9	005930-000	STD02Y-9		
+	6-1768041-4	STD02W-PLUS	9-1768041-9	STD02Y-PLUS		
-	6-1768041-1	STD02W-MINUS	9-1768041-4	STD02Y-MINUS		
/	003880-000	STD02W-SLASH	1768042-5	STD02Y-SLASH		
⏚	5-1768041-4	STD02W-EARTH	7-1768041-9	STD02Y-EARTH		
.	5-1768041-3	STD02W-DOT	7-1768041-7	STD02Y-DOT		
	5-1768041-0	STD02W-BLANK				

		Coloured markers			
Printed Marking		TCPN	Part Description	Packaging size	Packaging type
0	Black	1-1768037-4	STB02-0-0	300	Pre-loaded
1	Brown	1-1768037-7	STB02-1-1		
2	Red	2-1768037-0	STB02-2-2		
3	Orange	2-1768037-3	STB02-3-3		
5	Green	2-1768037-8	STB02-5-5		
6	Blue	3-1768037-1	STB02-6-6		
7	Purple	3-1768037-4	STB02-7-7		
8	Gray	3-1768037-7	STB02-8-8		

STD MARKERS – SIZE 03

- Snap-On Markers
- Marker size '03'
- Marker Width: 3.5 mm
- Character Height: 2.1 mm
- For Cable Dia: 1.9 – 2.6 mm *(0.07 – 0.10 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	**TCPN**	**Part Description**	**TCPN**	**Part Description**	**Packaging Qty (Pieces)**	**Packaging type**
A	167476-000	**STD03W-A**	345038-000	**STD03Y-A**	300	Pre-loaded
B	213166-000	**STD03W-B**	588040-000	**STD03Y-B**		
C	586908-000	**STD03W-C**	4-1768042-2	**STD03Y-C**		
D	845704-000	**STD03W-D**	4-1768042-4	**STD03Y-D**		
E	916196-000	**STD03W-E**	4-1768042-7	**STD03Y-E**		
F	032218-000	**STD03W-F**	886822-000	**STD03Y-F**		
G	122028-000	**STD03W-G**	5-1768042-1	**STD03Y-G**		
H	801234-000	**STD03W-H**	361720-000	**STD03Y-H**		
I	761148-000	**STD03W-I**	413464-000	**STD03Y-I**		
J	000666-000	**STD03W-J**	5-1768042-4	**STD03Y-J**		
K	384850-000	**STD03W-K**	657680-000	**STD03Y-K**		
L	053232-000	**STD03W-L**	5-1768042-6	**STD03Y-L**		
M	236988-000	**STD03W-M**	5-1768042-8	**STD03Y-M**		
N	581086-000	**STD03W-N**	6-1768042-1	**STD03Y-N**		
O	321874-000	**STD03W-0**	768714-000	**STD03Y-0**		
P	969958-000	**STD03W-P**	6-1768042-3	**STD03Y-P**		
Q	185576-000	**STD03W-Q**	755512-000	**STD03Y-Q**		
R	559060-000	**STD03W-R**	6-1768042-5	**STD03Y-R**		
S	376500-000	**STD03W-S**	992474-000	**STD03Y-S**		
T	006340-000	**STD03W-T**	6-1768042-8	**STD03Y-T**		
U	593358-000	**STD03W-U**	6-1768042-9	**STD03Y-U**		
V	875154-000	**STD03W-V**	7-1768042-0	**STD03Y-V**		
W	026896-000	**STD03W-W**	7-1768042-1	**STD03Y-W**		
X	593434-000	**STD03W-X**	666390-000	**STD03Y-X**		
Y	982978-000	**STD03W-Y**	7-1768042-2	**STD03Y-Y**		
Z	033694-000	**STD03W-Z**	956734-000	**STD03Y-Z**		
0	321874-000	**STD03W-0**	768714-000	**STD03Y-0**		
1	496764-000	**STD03W-1**	197036-000	**STD03Y-1**		
2	369880-000	**STD03W-2**	610528-000	**STD03Y-2**		
3	434716-000	**STD03W-3**	770010-000	**STD03Y-3**		
4	092790-000	**STD03W-4**	499680-000	**STD03Y-4**		
5	403072-000	**STD03W-5**	998356-000	**STD03Y-5**		
6	571230-000	**STD03W-6**	518144-000	**STD03Y-6**		
7	345774-000	**STD03W-7**	443352-000	**STD03Y-7**		
8	446638-000	**STD03W-8**	774414-000	**STD03Y-8**		
9	070440-000	**STD03W-9**	090056-000	**STD03Y-9**		
+	3-1768042-3	**STD03W-PLUS**	6-1768042-4	**STD03Y-PLUS**		
-	3-1768042-0	**STD03W-MINUS**	5-1768042-9	**STD03Y-MINUS**		
/	489958-000	**STD03W-SLASH**	6-1768042-7	**STD03Y-SLASH**		
⏚	351404-000	**STD03W-EARTH**	4-1768042-8	**STD03Y-EARTH**		
.	2-1768042-3	**STD03W-DOT**	4-1768042-6	**STD03Y-DOT**		
	2-1768042-0	**STD03W-BLANK**				

		Coloured markers			
Printed Marking		**TCPN**	**Part Description**	**Packaging size**	**Packaging type**
0	Black	4-1768037-8	**STB03-0-0**	300	Pre-loaded
1	Brown	5-1768037-3	**STB03-1-1**		
2	Red	5-1768037-8	**STB03-2-2**		
3	Orange	6-1768037-3	**STB03-3-3**		
5	Green	7-1768037-3	**STB03-5-5**		
6	Blue	7-1768037-8	**STB03-6-6**		
7	Purple	8-1768037-3	**STB03-7-7**		
8	Gray	8-1768037-8	**STB03-8-8**		

STD MARKERS – SIZE 05

- Snap-On Markers
- Marker size '05'
- Marker Width: 3.5 mm
- Character Height: 2.0 mm
- For Cable Dia: 2.3 – 3 mm *(0.09 – 0.12 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	8-1768042-3	STD05W-A	4-1768043-0	STD05Y-A	300	Pre-loaded
B	8-1768042-6	STD05W-B	4-1768043-3	STD05Y-B		
C	8-1768042-9	STD05W-C	4-1768043-6	STD05Y-C		
D	9-1768042-1	STD05W-D	4-1768043-8	STD05Y-D		
E	9-1768042-4	STD05W-E	5-1768043-1	STD05Y-E		
F	9-1768042-7	STD05W-F	5-1768043-4	STD05Y-F		
G	9-1768042-9	STD05W-G	5-1768043-6	STD05Y-G		
H	1768043-2	STD05W-H	5-1768043-8	STD05Y-H		
I	1768043-4	STD05W-I	6-1768043-0	STD05Y-I		
J	1768043-5	STD05W-J	6-1768043-1	STD05Y-J		
K	1768043-6	STD05W-K	6-1768043-2	STD05Y-K		
L	1768043-8	STD05W-L	6-1768043-4	STD05Y-L		
M	1-1768043-0	STD05W-M	6-1768043-6	STD05Y-M		
N	1-1768043-3	STD05W-N	6-1768043-9	STD05Y-N		
O	7-1768042-3	STD05W-0	3-1768043-0	STD05Y-0		
P	1-1768043-5	STD05W-P	7-1768043-1	STD05Y-P		
Q	1-1768043-7	STD05W-Q	7-1768043-3	STD05Y-Q		
R	1-1768043-8	STD05W-R	7-1768043-4	STD05Y-R		
S	2-1768043-0	STD05W-S	7-1768043-6	STD05Y-S		
T	2-1768043-2	STD05W-T	7-1768043-8	STD05Y-T		
U	2-1768043-3	STD05W-U	7-1768043-9	STD05Y-U		
V	2-1768043-5	STD05W-V	8-1768043-0	STD05Y-V		
W	2-1768043-6	STD05W-W	8-1768043-1	STD05Y-W		
X	2-1768043-7	STD05W-X	8-1768043-2	STD05Y-X		
Y	2-1768043-8	STD05W-Y	8-1768043-3	STD05Y-Y		
Z	2-1768043-9	STD05W-Z	8-1768043-4	STD05Y-Z		
0	7-1768042-3	STD05W-0	3-1768043-0	STD05Y-0		
1	7-1768042-4	STD05W-1	3-1768043-1	STD05Y-1		
2	7-1768042-5	STD05W-2	3-1768043-2	STD05Y-2		
3	7-1768042-6	STD05W-3	3-1768043-3	STD05Y-3		
4	7-1768042-7	STD05W-4	3-1768043-4	STD05Y-4		
5	7-1768042-8	STD05W-5	3-1768043-5	STD05Y-5		
6	7-1768042-9	STD05W-6	3-1768043-6	STD05Y-6		
7	8-1768042-0	STD05W-7	3-1768043-7	STD05Y-7		
8	8-1768042-1	STD05W-8	3-1768043-8	STD05Y-8		
9	8-1768042-2	STD05W-9	3-1768043-9	STD05Y-9		
+	1-1768043-6	STD05W-PLUS	7-1768043-2	STD05Y-PLUS		
-	1-1768043-1	STD05W-MINUS	6-1768043-7	STD05Y-MINUS		
/	2-1768043-1	STD05W-SLASH	7-1768043-7	STD05Y-SLASH		
⏚	9-1768042-5	STD05W-EARTH	5-1768043-2	STD05Y-EARTH		
.	9-1768042-3	STD05W-DOT	5-1768043-0	STD05Y-DOT		
	8-1768042-7	STD05W-BLANK	4-1768043-4	STD05Y-BLANK		

		Coloured markers			
Printed Marking		TCPN	Part Description	Packaging size	Packaging type
0	Black	1-1768038-7	STB05-0-0	300	Pre-loaded
1	Brown	1-1768038-8	STB05-1-1		
2	Red	1-1768038-9	STB05-2-2		
3	Orange	2-1768038-0	STB05-3-3		
5	Green	2-1768038-1	STB05-5-5		
6	Blue	2-1768038-2	STB05-6-6		
7	Purple	2-1768038-3	STB05-7-7		
8	Gray	2-1768038-4	STB05-8-8		

STD MARKERS – SIZE 06

- Snap-On Markers
- Marker size '06'
- Marker Width: 3.5 mm
- Character Height: 2.0 mm
- For Cable Dia: 2.6 – 3.5 mm *(0.10 – 0.13 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	465694-000	STD06W-A	087406-000	STD06Y-A	300	Pre-loaded
B	390550-000	STD06W-B	757816-000	STD06Y-B		
C	286932-000	STD06W-C	621660-000	STD06Y-C		
D	651444-000	STD06W-D	661096-000	STD06Y-D		
E	574158-000	STD06W-E	056868-000	STD06Y-E		
F	235542-000	STD06W-F	863870-000	STD06Y-F		
G	578874-000	STD06W-G	203428-000	STD06Y-G		
H	459916-000	STD06W-H	582580-000	STD06Y-H		
I	195488-000	STD06W-I	945988-000	STD06Y-I		
J	257040-000	STD06W-J	301972-000	STD06Y-J		
K	573384-000	STD06W-K	668832-000	STD06Y-K		
L	234826-000	STD06W-L	001308-000	STD06Y-L		
M	273236-000	STD06W-M	682660-000	STD06Y-M		
N	928608-000	STD06W-N	858346-000	STD06Y-N		
O	134056-000	STD06W-0	459072-000	STD06Y-0		
P	588992-000	STD06W-P	033374-000	STD06Y-P		
Q	168296-000	STD06W-Q	675790-000	STD06Y-Q		
R	455404-000	STD06W-R	168706-000	STD06Y-R		
S	220668-000	STD06W-S	074826-000	STD06Y-S		
T	819568-000	STD06W-T	836378-000	STD06Y-T		
U	639630-000	STD06W-U	816500-000	STD06Y-U		
V	683320-000	STD06W-V	709862-000	STD06Y-V		
W	015462-000	STD06W-W	976882-000	STD06Y-W		
X	061564-000	STD06W-X	424858-000	STD06Y-X		
Y	004924-000	STD06W-Y	067448-000	STD06Y-Y		
Z	217706-000	STD06W-Z	930240-000	STD06Y-Z		
0	134056-000	STD06W-0	459072-000	STD06Y-0		
1	712904-000	STD06W-1	474550-000	STD06Y-1		
2	478630-000	STD06W-2	493356-000	STD06Y-2		
3	991038-000	STD06W-3	444122-000	STD06Y-3		
4	662434-000	STD06W-4	805984-000	STD06Y-4		
5	531934-000	STD06W-5	092458-000	STD06Y-5		
6	177598-000	STD06W-6	226310-000	STD06Y-6		
7	632126-000	STD06W-7	677496-000	STD06Y-7		
8	384682-000	STD06W-8	729268-000	STD06Y-8		
9	965848-000	STD06W-9	978452-000	STD06Y-9		
+	1768044-7	STD06W-PLUS	E52054-000	STD06Y-PLUS		
-	1768044-4	STD06W-MINUS	2-1768044-9	STD06Y-MINUS		
/	094824-000	STD06W-SLASH	562584-000	STD06Y-SLASH		
⏚	9-1768043-5	STD06W-EARTH	2-1768044-1	STD06Y-EARTH		
.	9-1768043-4	STD06W-DOT	2-1768044-0	STD06Y-DOT		
	114376-000	STD06W-BLANK	1-1768044-6	STD06Y-BLANK		

		Coloured markers			
Printed Marking		TCPN	Part Description	Packaging size	Packaging type
0	Black	3-1768038-3	STB06-0-0	300	Pre-loaded
1	Brown	3-1768038-8	STB06-1-1		
2	Red	4-1768038-4	STB06-2-2		
3	Orange	5-1768038-0	STB06-3-3		
5	Green	6-1768038-0	STB06-5-5		
6	Blue	6-1768038-5	STB06-6-6		
7	Purple	7-1768038-1	STB06-7-7		
8	Gray	7-1768038-6	STB06-8-8		
9		965848-000	STD06Y-9		

STD MARKERS – SIZE 09

- Snap-On Markers
- Marker size '09'
- Marker Width: 3.5 mm
- Character Height: 2.0 mm
- For Cable Dia: 3.2 – 4.5 mm *(0.12 – 0.17 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	**TCPN**	**Part Description**	**TCPN**	**Part Description**	**Packaging Qty (Pieces)**	**Packaging type**
A	317872-000	**STD09W-A**	862816-000	**STD09Y-A**	300	Pre-loaded
B	929926-000	**STD09W-B**	036610-000	**STD09Y-B**		
C	595148-000	**STD09W-C**	452642-000	**STD09Y-C**		
D	535494-000	**STD09W-D**	281690-000	**STD09Y-D**		
E	318782-000	**STD09W-E**	882530-000	**STD09Y-E**		
F	778086-000	**STD09W-F**	017172-000	**STD09Y-F**		
G	362886-000	**STD09W-G**	112902-000	**STD09Y-G**		
H	659958-000	**STD09W-H**	075034-000	**STD09Y-H**		
I	234392-000	**STD09W-I**	769976-000	**STD09Y-I**		
J	429560-000	**STD09W-J**	327448-000	**STD09Y-J**		
K	594054-000	**STD09W-K**	672532-000	**STD09Y-K**		
L	591020-000	**STD09W-L**	509762-000	**STD09Y-L**		
M	853188-000	**STD09W-M**	205508-000	**STD09Y-M**		
N	547972-000	**STD09W-N**	667860-000	**STD09Y-N**		
O	808756-000	**STD09W-0**	047316-000	**STD09Y-0**		
P	294582-000	**STD09W-P**	597516-000	**STD09Y-P**		
Q	702368-000	**STD09W-Q**	247002-000	**STD09Y-Q**		
R	071620-000	**STD09W-R**	920140-000	**STD09Y-R**		
S	701134-000	**STD09W-S**	590022-000	**STD09Y-S**		
T	594256-000	**STD09W-T**	497634-000	**STD09Y-T**		
U	588548-000	**STD09W-U**	491394-000	**STD09Y-U**		
V	651644-000	**STD09W-V**	423154-000	**STD09Y-V**		
W	910358-000	**STD09W-W**	365646-000	**STD09Y-W**		
X	697154-000	**STD09W-X**	523918-000	**STD09Y-X**		
Y	068920-000	**STD09W-Y**	362942-000	**STD09Y-Y**		
Z	952914-000	**STD09W-Z**	322370-000	**STD09Y-Z**		
0	808756-000	**STD09W-0**	047316-000	**STD09Y-0**		
1	564314-000	**STD09W-1**	064090-000	**STD09Y-1**		
2	881128-000	**STD09W-2**	700690-000	**STD09Y-2**		
3	451612-000	**STD09W-3**	410908-000	**STD09Y-3**		
4	776688-000	**STD09W-4**	422172-000	**STD09Y-4**		
5	411220-000	**STD09W-5**	131226-000	**STD09Y-5**		
6	062724-000	**STD09W-6**	746782-000	**STD09Y-6**		
7	638470-000	**STD09W-7**	007980-000	**STD09Y-7**		
8	671050-000	**STD09W-8**	634544-000	**STD09Y-8**		
9	519158-000	**STD09W-9**	645636-000	**STD09Y-9**		
+	5-1768044-5	**STD09W-PLUS**	7-1768044-8	**STD09Y-PLUS**		
-	5-1768044-2	**STD09W-MINUS**	7-1768044-5	**STD09Y-MINUS**		
/	190726-000	**STD09W-SLASH**	792924-000	**STD09Y-SLASH**		
⏚	4-1768044-4	**STD09W-EARTH**	6-1768044-7	**STD09Y-EARTH**		
.	4-1768044-3	**STD09W-DOT**	6-1768044-6	**STD09Y-DOT**		
	4-1768044-0	**STD09W-BLANK**				

		Coloured markers			
Printed Marking		**TCPN**	**Part Description**	**Packaging size**	**Packaging type**
0	Black	1768039-4	**STB09-0-0**	300	Pre-loaded
1	Brown	1768039-6	**STB09-1-1**		
2	Red	1768039-9	**STB09-2-2**		
3	Orange	1-1768039-2	**STB09-3-3**		
5	Green	1-1768039-6	**STB09-5-5**		
6	Blue	1-1768039-8	**STB09-6-6**		
7	Purple	1-1768039-9	**STB09-7-7**		
8	Gray	2-1768039-0	**STB09-8-8**		

STD MARKERS – SIZE 12

- Snap-On Markers
- Marker size '12'
- Marker Width: 3.7 mm
- Character Height: 2.7 mm
- For Cable Dia: 4.5 - 6 mm *(0.17 – 0.23 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	392758-000	STD12W-A	1768045-9	STD12Y-A	300	Pre-loaded
B	190370-000	STD12W-B	1-1768045-2	STD12Y-B		
C	379242-000	STD12W-C	1-1768045-5	STD12Y-C		
D	466552-000	STD12W-D	1-1768045-7	STD12Y-D		
E	952178-000	STD12W-E	2-1768045-0	STD12Y-E		
F	242654-000	STD12W-F	2-1768045-3	STD12Y-F		
G	371912-000	STD12W-G	2-1768045-5	STD12Y-G		
H	544882-000	STD12W-H	2-1768045-7	STD12Y-H		
I	743644-000	STD12W-I	2-1768045-9	STD12Y-I		
J	925236-000	STD12W-J	3-1768045-0	STD12Y-J		
K	402858-000	STD12W-K	3-1768045-1	STD12Y-K		
L	372210-000	STD12W-L	3-1768045-3	STD12Y-L		
M	797170-000	STD12W-M	3-1768045-5	STD12Y-M		
N	224378-000	STD12W-N	3-1768045-8	STD12Y-N		
O	027608-000	STD12W-0	9-1768044-8	STD12Y-0		
P	200490-000	STD12W-P	4-1768045-0	STD12Y-P		
Q	881472-000	STD12W-Q	4-1768045-2	STD12Y-Q		
R	610526-000	STD12W-R	4-1768045-3	STD12Y-R		
S	958362-000	STD12W-S	4-1768045-5	STD12Y-S		
T	080248-000	STD12W-T	4-1768045-7	STD12Y-T		
U	606344-000	STD12W-U	4-1768045-8	STD12Y-U		
V	244058-000	STD12W-V	4-1768045-9	STD12Y-V		
W	922324-000	STD12W-W	5-1768045-0	STD12Y-W		
X	151660-000	STD12W-X	5-1768045-1	STD12Y-X		
Y	976192-000	STD12W-Y	5-1768045-2	STD12Y-Y		
Z	928688-000	STD12W-Z	5-1768045-3	STD12Y-Z		
0	027608-000	STD12W-0	9-1768044-8	STD12Y-0		
1	028690-000	STD12W-1	9-1768044-9	STD12Y-1		
2	127922-000	STD12W-2	1768045-1	STD12Y-2		
3	869998-000	STD12W-3	1768045-2	STD12Y-3		
4	422284-000	STD12W-4	1768045-3	STD12Y-4		
5	329976-000	STD12W-5	1768045-4	STD12Y-5		
6	654200-000	STD12W-6	1768045-5	STD12Y-6		
7	727782-000	STD12W-7	1768045-6	STD12Y-7		
8	157886-000	STD12W-8	1768045-7	STD12Y-8		
9	612832-000	STD12W-9	1768045-8	STD12Y-9		
+	9-1768044-6	STD12W-PLUS	4-1768045-1	STD12Y-PLUS		
-	9-1768044-3	STD12W-MINUS	3-1768045-6	STD12Y-MINUS		
/	102828-000	STD12W-SLASH	4-1768045-6	STD12Y-SLASH		
⏚	8-1768044-6	STD12W-EARTH	2-1768045-1	STD12Y-EARTH		
.	8-1768044-5	STD12W-DOT	1-1768045-9	STD12Y-DOT		
	8-1768044-2	STD12W-BLANK	1-1768045-3	STD12Y-BLANK		

		Coloured markers			
Printed Marking		TCPN	Part Description	Packaging size	Packaging type
0	Black	4-1768039-4	STB12-0-0	300	Pre-loaded
1	Brown	4-1768039-5	STB12-1-1		
2	Red	4-1768039-6	STB12-2-2		
3	Orange	4-1768039-7	STB12-3-3		
5	Green	4-1768039-8	STB12-5-5		
6	Blue	4-1768039-9	STB12-6-6		
7	Purple	5-1768039-0	STB12-7-7		
8	Gray	5-1768039-1	STB12-8-8		

STD MARKERS – SIZE 15

- Snap-On Markers
- Marker size '15'
- Marker Width: 5.6 mm
- Character Height: 3.0 mm
- For Cable Dia: 5.8 – 8.5mm *(0.22 – 0.33 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	755008-000	STD15W-A	8-1768045-4	STD15Y-A	50	Box
B	802902-000	STD15W-B	8-1768045-7	STD15Y-B		
C	838714-000	STD15W-C	9-1768045-0	STD15Y-C		
D	629606-000	STD15W-D	9-1768045-2	STD15Y-D		
E	133110-000	STD15W-E	9-1768045-5	STD15Y-E		
F	537002-000	STD15W-F	9-1768045-8	STD15Y-F		
G	685362-000	STD15W-G	1768046-1	STD15Y-G		
H	863976-000	STD15W-H	1768046-3	STD15Y-H		
I	913588-000	STD15W-I	1768046-5	STD15Y-I		
J	344640-000	STD15W-J	1768046-6	STD15Y-J		
K	501372-000	STD15W-K	1768046-7	STD15Y-K		
L	002648-000	STD15W-L	1768046-9	STD15Y-L		
M	347828-000	STD15W-M	1-1768046-1	STD15Y-M		
N	612672-000	STD15W-N	1-1768046-4	STD15Y-N		
O	5-1768045-5	STD15W-0	7-1768045-4	STD15Y-0		
P	388482-000	STD15W-P	1-1768046-6	STD15Y-P		
Q	621494-000	STD15W-Q	1-1768046-8	STD15Y-Q		
R	325234-000	STD15W-R	1-1768046-9	STD15Y-R		
S	544426-000	STD15W-S	2-1768046-1	STD15Y-S		
T	845482-000	STD15W-T	2-1768046-3	STD15Y-T		
U	126270-000	STD15W-U	2-1768046-4	STD15Y-U		
V	907764-000	STD15W-V	2-1768046-5	STD15Y-V		
W	071812-000	STD15W-W	2-1768046-6	STD15Y-W		
X	362816-000	STD15W-X	2-1768046-7	STD15Y-X		
Y	578440-000	STD15W-Y	2-1768046-8	STD15Y-Y		
Z	063698-000	STD15W-Z	2-1768046-9	STD15Y-Z		
0	5-1768045-5	STD15W-0	7-1768045-4	STD15Y-0		
1	916500-000	STD15W-1	7-1768045-5	STD15Y-1		
2	631526-000	STD15W-2	7-1768045-6	STD15Y-2		
3	883382-000	STD15W-3	7-1768045-7	STD15Y-3		
4	924992-000	STD15W-4	7-1768045-8	STD15Y-4		
5	381396-000	STD15W-5	7-1768045-9	STD15Y-5		
6	545292-000	STD15W-6	8-1768045-0	STD15Y-6		
7	360170-000	STD15W-7	8-1768045-1	STD15Y-7		
8	075056-000	STD15W-8	8-1768045-2	STD15Y-8		
9	054712-000	STD15W-9	8-1768045-3	STD15Y-9		
+	7-1768045-2	STD15W-PLUS	1-1768046-7	STD15Y-PLUS		
-	6-1768045-9	STD15W-MINUS	1-1768046-2	STD15Y-MINUS		
/	857128-000	STD15W-SLASH	2-1768046-2	STD15Y-SLASH		
⏚	6-1768045-2	STD15W-EARTH	9-1768045-6	STD15Y-EARTH		
.	6-1768045-1	STD15W-DOT	9-1768045-4	STD15Y-DOT		
	5-1768045-8	STD15W-BLANK				
	5-1768045-4	STD15-APPLICATOR				

		Coloured markers			
Printed Marking		TCPN	Part Description	Packaging size	Packaging type
0	Black	6-1768039-0	STB15-0-0	300	Pre-loaded
1	Brown	6-1768039-1	STB15-1-1		
2	Red	6-1768039-4	STB15-2-2		
3	Orange	6-1768039-7	STB15-3-3		
5	Green	7-1768039-0	STB15-5-5		
6	Blue	7-1768039-2	STB15-6-6		
7	Purple	7-1768039-3	STB15-7-7		
8	Gray	7-1768039-6	STB15-8-8		

STD MARKERS – SIZE 17

- Snap-On Markers
- Marker size '17'
- Marker Width: 6.0 mm
- Character Height: 3.9 mm
- For Cable Dia: 8.5 – 11.5 mm *(0.33 – 0.45 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	265752-000	STD17W-A	5-1768046-9	STD17Y-A	50	Box
B	810362-000	STD17W-B	6-1768046-2	STD17Y-B		
C	201082-000	STD17W-C	6-1768046-5	STD17Y-C		
D	579356-000	STD17W-D	6-1768046-7	STD17Y-D		
E	899028-000	STD17W-E	7-1768046-0	STD17Y-E		
F	519516-000	STD17W-F	7-1768046-3	STD17Y-F		
G	126680-000	STD17W-G	7-1768046-5	STD17Y-G		
H	435224-000	STD17W-H	7-1768046-7	STD17Y-H		
I	860516-000	STD17W-I	7-1768046-9	STD17Y-I		
J	608890-000	STD17W-J	8-1768046-0	STD17Y-J		
K	851872-000	STD17W-K	8-1768046-1	STD17Y-K		
L	336396-000	STD17W-L	8-1768046-3	STD17Y-L		
M	198170-000	STD17W-M	8-1768046-5	STD17Y-M		
N	160164-000	STD17W-N	8-1768046-8	STD17Y-N		
O	527604-000	STD17W-0	4-1768046-9	STD17Y-0		
P	206748-000	STD17W-P	9-1768046-0	STD17Y-P		
Q	826344-000	STD17W-Q	9-1768046-2	STD17Y-Q		
R	122436-000	STD17W-R	9-1768046-3	STD17Y-R		
S	755828-000	STD17W-S	9-1768046-5	STD17Y-S		
T	320388-000	STD17W-T	9-1768046-7	STD17Y-T		
U	888064-000	STD17W-U	9-1768046-8	STD17Y-U		
V	556206-000	STD17W-V	9-1768046-9	STD17Y-V		
W	670780-000	STD17W-W	1768047-1	STD17Y-W		
X	634758-000	STD17W-X	1768047-2	STD17Y-X		
Y	527804-000	STD17W-Y	1768047-3	STD17Y-Y		
Z	192346-000	STD17W-Z	1768047-4	STD17Y-Z		
0	527604-000	STD17W-0	4-1768046-9	STD17Y-0		
1	203994-000	STD17W-1	5-1768046-0	STD17Y-1		
2	183268-000	STD17W-2	5-1768046-1	STD17Y-2		
3	364638-000	STD17W-3	5-1768046-2	STD17Y-3		
4	901940-000	STD17W-4	5-1768046-3	STD17Y-4		
5	286422-000	STD17W-5	5-1768046-4	STD17Y-5		
6	630534-000	STD17W-6	5-1768046-5	STD17Y-6		
7	805758-000	STD17W-7	5-1768046-6	STD17Y-7		
8	117110-000	STD17W-8	5-1768046-7	STD17Y-8		
9	187054-000	STD17W-9	5-1768046-8	STD17Y-9		
+	4-1768046-7	STD17W-PLUS	9-1768046-1	STD17Y-PLUS		
-	4-1768046-4	STD17W-MINUS	8-1768046-6	STD17Y-MINUS		
/	777264-000	STD17W-SLASH	9-1768046-6	STD17Y-SLASH		
⏚	3-1768046-7	STD17W-EARTH	7-1768046-1	STD17Y-EARTH		
.	3-1768046-6	STD17W-DOT	6-1768046-9	STD17Y-DOT		
	3-1768046-3	STD17W-BLANK				
	3-1768046-0	STD17-APPLICATOR				

Coloured markers

Printed Marking		TCPN	Part Description	Packaging size	Packaging type
0	Black	1768040-4	STB17-0-0	300	Pre-loaded
1	Brown	1768040-6	STB17-1-1		
2	Red	1768040-8	STB17-2-2		
3	Orange	1-1768040-0	STB17-3-3		
5	Green	1-1768040-3	STB17-5-5		
6	Blue	1-1768040-5	STB17-6-6		
7	Purple	1-1768040-7	STB17-7-7		
8	Gray	1-1768040-9	STB17-8-8		
9		187054-000	STD17W-9		

STD MARKERS – SIZE 21

- Snap-On Markers
- Marker size '21'
- Marker Width: 7.6 mm
- Character Height: 4.5 mm
- For Cable Dia: 11 – 15.5 mm *(0.43 – 0.61 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	138262-000	STD21W-A	3-1768047-5	STD21Y-A	50	Box
B	846224-000	STD21W-B	3-1768047-8	STD21Y-B		
C	315560-000	STD21W-C	4-1768047-1	STD21Y-C		
D	937516-000	STD21W-D	4-1768047-3	STD21Y-D		
E	398254-000	STD21W-E	4-1768047-6	STD21Y-E		
F	150770-000	STD21W-F	4-1768047-9	STD21Y-F		
G	415068-000	STD21W-G	5-1768047-1	STD21Y-G		
H	872820-000	STD21W-H	5-1768047-3	STD21Y-H		
I	091456-000	STD21W-I	5-1768047-5	STD21Y-I		
J	210862-000	STD21W-J	5-1768047-6	STD21Y-J		
K	236972-000	STD21W-K	5-1768047-7	STD21Y-K		
L	144498-000	STD21W-L	5-1768047-9	STD21Y-L		
M	151926-000	STD21W-M	6-1768047-1	STD21Y-M		
N	148398-000	STD21W-N	6-1768047-4	STD21Y-N		
O	1768047-6	STD21W-0	2-1768047-5	STD21Y-0		
P	852494-000	STD21W-P	6-1768047-6	STD21Y-P		
Q	085934-000	STD21W-Q	6-1768047-8	STD21Y-Q		
R	962458-000	STD21W-R	6-1768047-9	STD21Y-R		
S	251560-000	STD21W-S	7-1768047-1	STD21Y-S		
T	650510-000	STD21W-T	7-1768047-3	STD21Y-T		
U	461542-000	STD21W-U	7-1768047-4	STD21Y-U		
V	023470-000	STD21W-V	7-1768047-5	STD21Y-V		
W	034464-000	STD21W-W	7-1768047-6	STD21Y-W		
X	316680-000	STD21W-X	7-1768047-7	STD21Y-X		
Y	882830-000	STD21W-Y	7-1768047-8	STD21Y-Y		
Z	475522-000	STD21W-Z	7-1768047-9	STD21Y-Z		
0	1768047-6	STD21W-0	2-1768047-5	STD21Y-0		
1	303184-000	STD21W-1	2-1768047-6	STD21Y-1		
2	563918-000	STD21W-2	2-1768047-7	STD21Y-2		
3	884468-000	STD21W-3	2-1768047-8	STD21Y-3		
4	666714-000	STD21W-4	2-1768047-9	STD21Y-4		
5	263556-000	STD21W-5	3-1768047-0	STD21Y-5		
6	557678-000	STD21W-6	3-1768047-1	STD21Y-6		
7	375434-000	STD21W-7	3-1768047-2	STD21Y-7		
8	871050-000	STD21W-8	3-1768047-3	STD21Y-8		
9	025278-000	STD21W-9	3-1768047-4	STD21Y-9		
+	2-1768047-3	STD21W-PLUS	6-1768047-7	STD21Y-PLUS		
-	2-1768047-0	STD21W-MINUS	6-1768047-2	STD21Y-MINUS		
/	764286-000	STD21W-SLASH	7-1768047-2	STD21Y-SLASH		
⏚	1-1768047-3	STD21W-EARTH	4-1768047-7	STD21Y-EARTH		
.	1-1768047-2	STD21W-DOT	4-1768047-5	STD21Y-DOT		
	1768047-9	STD21W-BLANK	3-1768047-9	STD21Y-BLANK		
	1768047-5	STD21-APPLICATOR				

Coloured markers

Printed Marking		TCPN	Part Description	Packaging size	Packaging type
0	Black	5-1768040-0	STB21-BLANK-0	300	Pre-loaded
1	Brown	-	-		
2	Red	5-1768040-2	STB21-BLANK-2		
3	Orange	5-1768040-3	STB21-BLANK-3		
5	Green	-	-		
6	Blue	-	-		
7	Purple	5-1768040-5	STB21-BLANK-6		
8	Gray	-	-		

STD MARKERS – SIZE 24

- Snap-On Markers
- Marker size '24'
- Marker Width: 17.6 mm
- Character Height: 5.3 mm
- For Cable Dia: 15 – 19 mm *(0.59 – 0.74 Inch)*

	White color / Printed black		Yellow color / Printed black			
Printed Marking	TCPN	Part Description	TCPN	Part Description	Packaging Qty (Pieces)	Packaging type
A	197264-000	STD24W-A	031882-000	STD24Y-A	50	Box
B	314578-000	STD24W-B	336486-000	STD24Y-B		
C	946230-000	STD24W-C	104986-000	STD24Y-C		
D	339676-000	STD24W-D	802932-000	STD24Y-D		
E	398232-000	STD24W-E	1-1768048-0	STD24Y-E		
F	549392-000	STD24W-F	1-1768048-3	STD24Y-F		
G	928554-000	STD24W-G	1-1768048-5	STD24Y-G		
H	917568-000	STD24W-H	1-1768048-7	STD24Y-H		
I	901502-000	STD24W-I	1-1768048-9	STD24Y-I		
J	687814-000	STD24W-J	2-1768048-0	STD24Y-J		
K	732956-000	STD24W-K	2-1768048-1	STD24Y-K		
L	759108-000	STD24W-L	320608-000	STD24Y-L		
M	301210-000	STD24W-M	2-1768048-4	STD24Y-M		
N	817492-000	STD24W-N	2-1768048-7	STD24Y-N		
O	8-1768047-1	STD24W-0	1768048-2	STD24Y-0		
P	968824-000	STD24W-P	2-1768048-9	STD24Y-P		
Q	399170-000	STD24W-Q	3-1768048-1	STD24Y-Q		
R	464414-000	STD24W-R	833408-000	STD24Y-R		
S	040998-000	STD24W-S	3-1768048-3	STD24Y-S		
T	264594-000	STD24W-T	3-1768048-5	STD24Y-T		
U	154936-000	STD24W-U	3-1768048-6	STD24Y-U		
V	271808-000	STD24W-V	3-1768048-7	STD24Y-V		
W	116634-000	STD24W-W	3-1768048-8	STD24Y-W		
X	233500-000	STD24W-X	3-1768048-9	STD24Y-X		
Y	138132-000	STD24W-Y	4-1768048-0	STD24Y-Y		
Z	840894-000	STD24W-Z	4-1768048-1	STD24Y-Z		
0	8-1768047-1	STD24W-0	1768048-2	STD24Y-0		
1	866522-000	STD24W-1	340014-000	STD24Y-1		
2	640576-000	STD24W-2	805844-000	STD24Y-2		
3	417638-000	STD24W-3	123558-000	STD24Y-3		
4	542894-000	STD24W-4	081620-000	STD24Y-4		
5	978190-000	STD24W-5	201302-000	STD24Y-5		
6	905034-000	STD24W-6	532738-000	STD24Y-6		
7	273650-000	STD24W-7	579826-000	STD24Y-7		
8	187136-000	STD24W-8	918298-000	STD24Y-8		
9	394338-000	STD24W-9	537750-000	STD24Y-9		
+	9-1768047-9	STD24W-PLUS	3-1768048-0	STD24Y-PLUS		
-	9-1768047-6	STD24W-MINUS	2-1768048-5	STD24Y-MINUS		
/	716408-000	STD24W-SLASH	3-1768048-4	STD24Y-SLASH		
⏚	8-1768047-9	STD24W-EARTH	1-1768048-1	STD24Y-EARTH		
.	8-1768047-8	STD24W-DOT	1768048-9	STD24Y-DOT		
	8-1768047-4	STD24W-BLANK	1768048-5	STD24Y-BLANK		
	8-1768047-0	STD24-APPLICATOR				

Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need.
Visit **www.te.com/support** to chat with a Product Information Specialist.

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2021 TE Connectivity. All Rights Reserved.

ELECTRICAL / STD/STB-TYPE WIRE & CABLE MARKERS / BROCHURE / EN **09/21**

PRODUCT SHEET

TE Connectivity
3, rue Jean Perrin

69687 Chassieu cedex

France

Tel: +33 481923100