

Data sheet | Item number: 756-9212/040-000


Connectors for sensor/actuator cable; M12 socket, straight; 4-pole


www.wago.com/756-9212/040-000



RoHS 
Compliant

[BOMcheck.net](https://www.bomcheck.net)





Anschließbare Leitung
Ø 4 ... 6 mm / 0,14 - 0,50 mm²

Data

Technical Data

Connection type	M12 socket
No. of poles	4
Cable connection direction to mating direction	0°
Connector interface coding cable/adaptor 1 1	A coded

Connection data

Connection type (1)	Federtechnik
Solid conductor	0.14 ... 0.5 mm ² / ...

Mechanical data

Connectable sheathed cable diameter	4 ... 6 mm
Weight	25.3 g

Environmental Requirements

Degree of protection	IP67
----------------------	------



Commercial data

Country of origin	DE
GTIN	4045454695118
Customs Tariff No.	85369010000

Downloads

Documentation

System Description

IP67 Cables and Pluggable Connectors	Jun 6, 2017	Download
		434.4 kB

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.