

**GWDR NP (flat gasket - neoprene)
GWDR M32-NP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

General ordering data

Type	GWDR M32-NP
Order No.	1736260000
Version	GWDR NP (flat gasket - neoprene), Sealing ring, M 32, Neoprene
GTIN (EAN)	4008 190956059
Qty.	50 pc(s).

GWDR NP (flat gasket - neoprene)
GWDR M32-NP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Net weight	1.36 g
------------	--------

General information

Material	Neoprene	Cable glands	metric
External thread	M 32	Pitch of thread	1.5 mm
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Thickness	1.5 mm	Inside diameter D2	32 mm
Diameter of sealing ring	42 mm		

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
eClass 9.0	27-43-03-19	eClass 9.1	27-14-44-90
eClass 10.0	27-43-03-19	UNSPSC	31-16-18-18

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

GWDR NP (flat gasket - neoprene) **GWDR M32-NP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

