



General ordering data

Order No.	1873291000
Part designation	SAIL-M5BG-3P-10U
Version	Sensor/Actuator line, One end without connector, LED: No, 10.00 m, PUR/PVC
EAN	4032248480067
Qty.	1 pc(s).

Technical data

Ambient temperature, max.	80 °C
Ambient temperature, min.	-25 °C
Cable diameter, max.	5 mm
Cable diameter, min	4.6 mm
Connection cross-section	0.25
Contact material	Ni/Au
Contact surface	gold-plated
Contact tube diameter	M5
Core cross-section	0.25 mm ²
Material	PUR/PVC
Pollution severity	3
Protection class	IP 67
Rated current	1 A
Rated voltage	125 V
Sheathing colour	black
Suitable for cable carriers	Yes
Wiring diagram	
No. of poles	3
Version	Female socket, straight
Cable length	10 m

Classifications

ETIM 2.0	EC000304
ETIM 3.0	EC001855
eClass 4.1	27-06-00-00
eClass 5.0	27-06-91-90

Classifications

eClass 5.1

27-06-91-90

Similar products

Order No.	Part designation	Version
1873290150	SAIL-M5BG-3P-1.5U	Sensor/Actuator line, One end without connector, LED: No, 1.50 m, PUR/PVC
1873290300	SAIL-M5BG-3P-3.0U	Sensor/Actuator line, One end without connector, LED: No, 3.00 m, PUR/PVC
1873290500	SAIL-M5BG-3P-5.0U	Sensor/Actuator line, One end without connector, LED: No, 5.00 m, PUR/PVC