

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130013-0238](#)
Status: **Active**
Overview: [Brad® Mini-Change® Connectors](#)
Description: Mini-Change® A-Size Receptacle, 3 Poles, 1/2" - 14 NPT Threads, Male (Straight) to 16 AWG Leads, 0.305m (1.0') Length, IEC Code

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Receptacles
Series [130013](#)
IP Rating IP67
NEMA Rating NEMA 6
Overview [Brad® Mini-Change® Connectors](#)
Product Name Mini-Change®
Type Single Ended (pigtail)
UPC 78678841800

Physical

Coupling Type External Thread
Gender Male
Keyway Single
Length 0.305m
Material - Component Zinc Die-Cast with Black Epoxy
Mounting Thread Size 1/2" - 14 NPT
Orientation Straight
Panel Mount Front
Poles 3
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 16
Wire/Cable Type E152210

Electrical


Current - Maximum per Contact 13.0A
Voltage - Maximum 600V AC/DC

Material Info

Old Part Number 1R3006A25A120

Reference - Drawing Numbers

Sales Drawing SD-130013-023



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[130013Series](#)