



Part Number : [1301540001](#)
Product Description : Super-Safeway Standard
Molded W Cordset, 3 Pole/3 Wire SOOW Cordset,
Cordset Length 0.91m (3.0'), Non-NEMA, 250V
Series Number : 130154
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 09588

Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130154
Description	Super-Safeway Standard Molded W Cordset, 3 Pole/3 Wire SOOW Cordset, Cordset Length 0.91m (3.0'), Non-NEMA, 250V
IP Rating	IP44
NEMA Configuration	Non-NEMA
Product Name	Safeway
Specialty	N/A
Type	Molded W Cordset
UPC	78678808587

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No
Locking Blade	Yes
Poles	3-pole/3-wire
Receptacle Type	N/A