



Part Number : [1200790190](#)

Product Description : Ultra-Lock (M12) Single-Ended Cordset, 4 Poles, Male (90°) to Pigtail, 22 AWG, PVC Cable, 6.0m (19.68') Length

Series Number : 120079

Status : Obsolete

Product Category : Circular Industrial Cordsets

Engineering Part Number : W04007A09M060

Documents and Resources

Drawings

[1200790190_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

Part Details

General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	120079
Description	Ultra-Lock (M12) Single-Ended Cordset, 4 Poles, Male (90°) to Pigtail, 22 AWG, PVC Cable, 6.0m (19.68') Length
IP Rating	IP69K
Product Name	Ultra-Lock (M12)
Protocol	EtherNet
Type	Single Ended
UPC	78678884764

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.33mm (.210")
Cable Length	6.0m (19.68')
Color - Cable Jacket	Yellow
Connector End A	Ultra-Lock (M12)
Connector End B	Pigtail
Coupling Style	Push to Lock
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR

Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22

This document was generated on Feb 26, 2026

Obsolete