



Part Number : 1200800008
Product Description : Ultra-Lock (M12) In-Line Splitter Cordset, 4 Poles, 3-Female (Straight) to 4-Male (90°), PVC Cable, 2.0m Length
Series Number : 120080
Status : Obsolete
Product Category : Industrial Tees and Splitters
Engineering Part Number : WW4A31A09M020



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Industrial Tees and Splitters
Series	120080
Description	Ultra-Lock (M12) In-Line Splitter Cordset, 4 Poles, 3-Female (Straight) to 4-Male (90°), PVC Cable, 2.0m Length
IP Rating	IP68
Product Name	Ultra-Lock (M12)
Type	Splitter - In-line
UPC	78678887288

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Color - Cable Jacket	Yellow
Drop Connector	Ultra-Lock (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	None
Left Trunk Connector	Ultra-Lock (M12)
Left Trunk Gender	Female
Leg 1 Length	2.0m
Leg 2 Length	2.0m
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Nickel-plated Brass
Poles	3 Female/4 Male

Right Trunk Connector	Ultra-Lock (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-30°C to +90°C

This document was generated on Feb 27, 2026

Obsolete