



**Part Number :** [1300960052](#)

**Product Description :** Liquid-Tight Grip Strain Relief,  
1" NPT, 90° Angle Male, Mesh Length 0.133m (5.25")

**Series Number :** 130096

**Status :** Obsolete

**Product Category :** Cable Grips

**Engineering Part Number :** 36402



---

## Documents and Resources

### Drawings

[1300960052\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

|              |                                                                                     |
|--------------|-------------------------------------------------------------------------------------|
| Status       | Obsolete                                                                            |
| Category     | Cable Grips                                                                         |
| Series       | 130096                                                                              |
| Description  | Liquid-Tight Grip Strain Relief, 1" NPT, 90° Angle Male, Mesh Length 0.133m (5.25") |
| NEMA Rating  | NEMA 4                                                                              |
| Product Name | Liquid-Tight                                                                        |
| Type         | Strain Relief Grip                                                                  |
| UPC          | 78678836402                                                                         |

### Agency

|     |         |
|-----|---------|
| CSA | LR32159 |
| UL  | E61303  |

### Physical

|                            |                                   |
|----------------------------|-----------------------------------|
| Approximate Break Strength | N/A                               |
| Bale Length                | N/A                               |
| Body Style                 | 90° Angle                         |
| Cable Diameter             | N/A                               |
| Color - Grommet            | N/A                               |
| Eye Type                   | N/A                               |
| Gender                     | Male                              |
| Material - Body            | Malleable Iron, Zinc Plated Steel |
| Material - Grip            | Stainless Steel                   |
| Mesh Length                | 0.133m (5.25")                    |
| Net Weight                 | 279.640/g                         |
| Number of Holes            | N/A                               |
| O-Ring                     | N/A                               |
| Thread Size                | 1" NPT                            |

### Mates With / Use With

**Use with Part(s)**

| Description                                | Part Number       |
|--------------------------------------------|-------------------|
| MAX-LOC Lock Nut 1" NPT                    | <u>1300990145</u> |
| MAX-LOC Gasket Sealing Ring, 1" NPT, Black | <u>1300990151</u> |
| MAX-LOC O-Ring, 1" NPT                     | <u>1301800334</u> |

---

This document was generated on May 19, 2026

Obsolete