




RIP-TIE® Cable Management Center





Rip-Tie CableWrap



- **Fast!** Installs in seconds.
- **Easy!** Handy pull-tab release allows you to rearrange cable groupings with ease.
- **Tidy!** Keeps cables neatly and safely out of your way.



SIZE GUIDE

1. These recommendations are based on mating the full length of the hook section of the CableWrap in order to achieve maximum strength.
2. Two important variables are the diameter of the cable and the coil diameter, both will effect the proper choice of Rip-Tie length to match the cable length.
3. This is only a guide. You may find that your experience will vary.

Size	Diameter	Description
5/8" x 6" L6	1-1/2"	This narrow Rip-Tie CableWrap organizes short, lightweight cables under 10 ft in length including cords to small electrical appliances, patch cables, and small extension cords. It is ideal for Laptop computer accessories.
1" x 3" H3	3/4"	This short heavy duty Rip-Tie CableWrap is for short cables where extra strength is required. It is the shortest Rip-Tie CableWrap for cords less than 5 ft long.
1" x 6" H6	1-1/2"	This is the universal medium size Rip-Tie CableWrap. It organizes cords on small appliances and portable power tools, removable power cables, short extension cables and most cables up to 25ft long.
1" x 9" H9	2-1/4"	This medium long Rip-Tie CableWrap is for use on extension cords and power cables from 20-30 ft., pneumatic hose up to 15 ft long.
1" x 14" H14	3-3/4"	This long, heavy duty Rip-Tie CableWrap organizes large heavy duty extension cables (i.e. 12/3) up to 50 ft. This is the industrial standard for companies that use portable heavy duty equipment.
1" x 21" H21	5-1/2"	Use this Rip-Tie CableWrap for 75-100 ft. cables, pneumatic hoses, water hoses and other larger diameter materials.
2" x 18" E18	4"	This Rip-Tie CableWrap is for those demanding greater strength for their cables and hose bundles; typically, welding cables and other heavy industrial uses. They are double grommetted for attachment with two 50 lbs nylon ties, and features a protective flap to cover the nylon tie heads.
2" x 24" E24	6-1/2"	Same features as the E18 but LONGER for larger coils.
2" x 30" E30	8-1/2"	Same features as the E18 but LONGER for larger coils.
2" x 36" E36	10-1/2"	Longest CableWrap for heavy duty stranded power distribution cable.



- Patented...one end permanently attaches to the cable...the other end has a pull tab to free the Rip-Tie with one hand.
- Durable, made of the best quality hook and loop touch fastener...tested for 10,000 closures with no loss of holding strength.
- Used in many industries and by home users, wherever it is important to secure cables, keep them organized, and eliminate cable safety hazards.
- 11 sizes, 14 colors, plus the Rainbow Pack...all ten colors of the EIA Code in one package.
- Reusable and permanent...won't add non-recyclable materials to the environment. You can stop throwing cut plastic ties away.



CATALOG NUMBER	SIZE	UNIT	COLOR
M-06-1PK-BK M-06-010-BK M-06-100-BK	3/4" X 6"	1-Pack 10-Pack 100-Pack	Black Only
L-06-1PK- L-06-003- L-06-010- L-06-100-	5/8" X 6"	1-Pack 3-Pack 10-Pack 100-Pack	Black - BK
H-03-1PK- H-03-003- H-03-010- H-03-100-	1" X 3"	1-Pack 3-Pack 10-Pack 100-Pack	Blue - BU
H-06-1PK- H-06-003- H-06-010- H-06-100-	1" X 6"	1-Pack 3-Pack 10-Pack 100-Pack	Brown - BN
H-09-1PK- H-09-003- H-09-010- H-09-100-	1" X 9"	1-Pack 3-Pack 10-Pack 100-Pack	Green - GN
H-14-1PK- H-14-003- H-14-010- H-14-100-	1" X 14"	1-Pack 3-Pack 10-Pack 100-Pack	Grey - GY
H-21-1PK- H-21-003- H-21-010- H-21-100-	1" X 21"	1-Pack 3-Pack 10-Pack 100-Pack	Orange - O
E-18-1PK- E-18-010- E-18-050-	2" X 18"	1-Pack 10-Pack 50-Pack	Red - RD
E-24-1PK- E-24-010- E-24-050-	2" X 24"	1-Pack 10-Pack 50-Pack	Violet - V
E-30-1PK- E-30-010- E-30-050-	2" X 30"	1-Pack 10-Pack 50-Pack	White - W
E-36-1PK- E-36-010- E-36-050-	2" X 36"	1-Pack 10-Pack 50-Pack	Yellow - Y
			or Rainbow - RW (10 Colors)
			NEW!! NEON COLORS*
			Neon Green - NG
			Neon Orange - NO
			Neon Pink - NP
			Neon Yellow - NY
			*available in 1" width only

Rip-Tie CableWrap can be customized with company names and logos. See page 16 for details.



Rip-Tie CableCatch

Organize Cables Against a Surface





Adhesive backing permanently adheres to any smooth, flat surface. CableCatches have a convenient pull tab for fast and easy release.

The Rip-Tie CableCatch allows the user to change or move cables easily just by pulling the tab - only one hand is needed.

Rip-Tie CableCatches are available in 10 colors. This allows for easy identification of cables by color.

CATALOG NUMBER	SIZE	UNIT	COLOR
A-02-002- A-02-005- A-02-050-	5/8" X 2"	2-Pack 5-Pack 50-Pack	Black - BK Grey - GY White - W Only
A-04-002- A-04-005- A-04-050-	5/8" X 4"	2-Pack 5-Pack 50-Pack	Black - BK Blue - BU Brown - BN Green - GN Grey - GY Orange - O Red - RD Violet - V White - W Yellow - Y or Rainbow* - RW (10 Colors) <i>*50 Pack Only</i>
C-02-002- C-02-005- C-02-050-	1" X 2"	2-Pack 5-Pack 50-Pack	
C-04-002- C-04-005- C-04-050-	1" X 4"	2-Pack 5-Pack 50-Pack	
C-08-002- C-08-005- C-08-050-	1" X 8"	2-Pack 5-Pack 50-Pack	
C-12-002- C-12-005- C-12-050-	1" X 12"	2-Pack 5-Pack 50-Pack	

- Anchor cords, cables and wires neatly along surfaces and out of the way.
- Acrylic pressure sensitive adhesive securely attaches to equipment racks, desks, or walls.
- Peel-away backing makes the CableCatch easy to install.
- "Soft Hold" of the CableCatch successfully maintains the integrity of the cable performance.
- CableCatch offers an easy and reliable way to organize high performance data cables without using nylon ties.
- One quick pull of the tab releases the bundle for easy rearranging and quick equipment set-ups.
- Reusable and environmentally friendly, no more throwing away nylon cable ties.



Rip-Tie CableHanger

*Introducing a brand new solution
for suspending your cable woes*







The patented design locks the CableHanger firmly onto a vertical post. An extra heavy duty 50 lb. nylon tie is supplied to lock it in place. The CableHangers are easily released and retied, so adding, subtracting and replacing cables is a snap. Hook and Loop fasteners are gentle and will preserve the integrity of structured cabling and Fiber Optics.

CATALOG NUMBER	SIZE	UNIT	COLOR
S-03-1PK- S-03-010- S-03-100-	1" X 3"	1-Pack 10-Pack 100-Pack	Black - BK Blue - BU Brown - BN Green - GN Grey - GY Orange - O Red - RD Violet - V White - W Yellow - Y or Rainbow* - RW (10 Colors)
S-06-1PK- S-06-010- S-06-100-	1" X 6"	1-Pack 10-Pack 100-Pack	NEW!! NEON COLORS Neon Green - NG Neon Orange - NO Neon Pink - NP Neon Yellow - NY
S-09-1PK- S-09-010- S-09-100-	1" X 9"	1-Pack 10-Pack 100-Pack	
S-14-1PK- S-14-010- S-14-100-	1" X 14"	1-Pack 10-Pack 100-Pack	
S-21-1PK- S-21-010- S-21-100-	1" X 21"	1-Pack 10-Pack 100-Pack	

- "Soft Hold" of Hook & Loop instead of plastic wire ties.
- Attaches permanently to a vertical post and then wraps around the cable bundle. Keep grouped runs segregated from each other.
- Available in 14 colors and several sizes.
- Perfect for use in computer room subfloors.

CableHanger

Rip-Tie CableHanger can be customized with company names and logos. See page 16 for details.





Rip-Tie CinchStrap

We've made wrapping it up a cinch.

CinchStrap is a heavy duty utility strap with extra strength and holding power that exemplifies our exacting standards for the best quality. We use only the highest quality materials and double stitch - never glue or heat weld - to insure the CinchStrap will hold up to years of heavy use.

There are thousands of possible applications for industrial and home use.

- Designed for strength and dependability.
- Non-metallic - can be used safely around electrical equipment without causing short circuits, and around computers without demagnetizing disks.
- Extra Strength and infinitely adjustable sizes from 1" X 9" to 2" X 96" (14 sizes) and available in 14 colors.
- Has fabric pull-tab for ease of use.

Customized versions available for equipment strapping applications (Minimum 100pcs)




Rip-Tie CinchStrap can be customized with company names and logos. See page 16 for details.

CATALOG NUMBER	SIZE	UNIT	COLOR
N-09-1PK- N-09-010- N-09-100-	1" X 9"	1-Pack 10-Pack 100-Pack	Black - BK Blue - BU Brown - BN Green - GN Grey - GY Orange - O Red - RD Violet - V White - W Yellow - Y or Rainbow* - RW (10 Colors)
N-12-1PK- N-12-010- N-12-100-	1" X 12"	1-Pack 10-Pack 100-Pack	
N-18-1PK- N-18-010- N-18-100-	1" X 18"	1-Pack 10-Pack 100-Pack	
N-24-1PK- N-24-010- N-24-100-	1" X 24"	1-Pack 10-Pack 100-Pack	
N-30-1PK- N-30-010- N-30-100-	1" X 30"	1-Pack 10-Pack 100-Pack	
N-36-1PK- N-36-010- N-36-100-	1" X 36"	1-Pack 10-Pack 100-Pack	
N-48-1PK- N-48-010- N-48-100-	1" X 48"	1-Pack 10-Pack 100-Pack	
O-18-1PK- O-18-010- O-18-050-	2" X 18"	1-Pack 10-Pack 50-Pack	
O-24-1PK- O-24-010- O-24-050-	2" X 24"	1-Pack 10-Pack 50-Pack	
O-30-1PK- O-30-010- O-30-050-	1" X 30"	1-Pack 10-Pack 50-Pack	
O-36-1PK- O-36-010- O-36-050-	2" X 36"	1-Pack 10-Pack 50-Pack	
O-48-1PK- O-48-010- O-48-050-	2" X 48"	1-Pack 10-Pack 50-Pack	
O-72-1PK- O-72-010- O-72-050-	2" X 72"	1-Pack 10-Pack 50-Pack	
O-96-1PK- O-96-010- O-96-050-	2" X 96"	1-Pack 10-Pack 50-Pack	

NEW!!
NEON COLORS


- Neon Green - NG
- Neon Orange - NO
- Neon Pink - NP
- Neon Yellow - NY

- Black - BK
- Blue - BU
- Brown - BN
- Green - GN
- Grey - GY
- Orange - O
- Red - RD
- Violet - V
- White - W
- Yellow - Y
- or
- Rainbow* - RW
(10 Colors)



Rip-Tie CinchStrap-EG

Cable Management for Professionals.



CATALOG NUMBER	SIZE	UNIT	COLOR
N-07-G02- N-07-G10- N-07-G50-	1" X 7"	2-Pack 10-Pack 50-Pack	Black - BK Blue - BU Brown - BN Green - GN Grey - GY Orange - O Red - RD Violet - V White - W Yellow - Y or Rainbow* - RW (10 Colors)
N-10-G02- N-10-G10- N-10-G50-	1" X 10"	2-Pack 10-Pack 50-Pack	
N-16-G02- N-16-G10- N-16-G50-	1" X 16"	2-Pack 10-Pack 50-Pack	
N-22-G02- N-22-G10- N-22-G50-	1" X 22"	2-Pack 10-Pack 50-Pack	
N-28-G02- N-28-G10- N-28-G50-	1" X 28"	2-Pack 10-Pack 50-Pack	
N-34-G02- N-34-G10- N-34-G50-	1" X 34"	2-Pack 10-Pack 50-Pack	
N-46-G02- N-46-G10- N-46-G50-	1" X 46"	2-Pack 10-Pack 50-Pack	
O-16-G1P- O-16-G10- O-16-G50-	2" X 16"	1-Pack 10-Pack 50-Pack	
O-22-G1P- O-22-G10- O-22-G50-	2" X 22"	1-Pack 10-Pack 50-Pack	
O-28-G1P- O-28-G10- O-28-G50-	2" X 28"	1-Pack 10-Pack 50-Pack	
O-34-G1P- O-34-G10- O-34-G50-	2" X 34"	1-Pack 10-Pack 50-Pack	
O-46-G1P- O-46-G10- O-46-G50-	2" X 46"	1-Pack 10-Pack 50-Pack	
O-70-G1P- O-70-G10- O-70-G50-	2" X 70"	1-Pack 10-Pack 50-Pack	
O-94-G1P- O-94-G10- O-94-G50-	2" X 94"	1-Pack 10-Pack 50-Pack	

**NEW!!
NEON COLORS**





Neon Green - NG
Neon Orange - NO
Neon Pink - NP
Neon Yellow - NY

The CinchStrap-EG lets you take the stress off horizontal cable runs and safely organize cables from wiring racks, mobile carts, along walls, over doorways and in wiring closets.

Made from durable hook and loop material and a solid brass spur grommet. Features double stitching and fabric pull-tab.

- Attaches to any rack or surface. Use any fastener up to 1/4" diameter for mounting.
- Buckle cinch gives you more leverage.
- Brass grommet. Non-magnetic grommet spreads fastener load evenly without risk of ripping fabric.
- Durable hook and loop material lets you reorganize cables over and over again, up to 10,000 times.
- Sizes to meet every demand from 1" X 7" to 2" X 94" (14 sizes) and available in 14 colors.

Rip-Tie CinchStrap-EG can be customized with company names and logos. See page 16 for details.



CinchStrap-EG





Rip-Tie Lite & WrapStrap

Light Duty, Low Cost

Rip-Tie Lite - A Reusable CableWrap




- The Rip-Tie Lite is ideal for bundling & organizing computer and network cables.
- Rip-Tie Lite is made of one piece of double-sided hook and loop fastener. It has a die-cut slot for attachment to a single cable.
- Rip-Tie Lite is good for 200 - 300 refastenings.
- Rip-Tie Lite is perfect for use on equipment, home theatre and audio systems, appliances and more.



- The Rip-Tie Lite ScrewMount version has a larger head and a perforated "X" for driving a screw.


CATALOG NUMBER	SIZE	UNIT	COLOR
Y-05-010- Y-05-XRL- Y-05-144-	1/2" X 5"	10-Pack 10rls of 10 rls of 1440	Black - BK
Y-06-010- Y-06-XRL- Y-06-120-	1/2" X 6"	10-Pack 10rls of 10 rls of 1200	Blue - BU Brown - BN
Y-08-010- Y-08-XRL- Y-08-900-	1/2" X 8"	10-Pack 10rls of 10 rls of 900	Green - GN Grey - GY
Y-12-010- Y-12-XRL- Y-12-600-	1/2" X 12"	10-Pack 10rls of 10 rls of 600	Orange - O Red - RD
Y-18-010- Y-18-XRL- Y-18-400-	1/2" X 18"	10-Pack 10rls of 10 rls of 400	Violet - V White - W
RIP-TIE LITE SCREW MOUNT			
X-08-010- X-08-XRL- X-08-675-	1/2" X 8"	10-Pack 10rls of 10 rls of 675	Yellow - Y or Rainbow* - RW (10 Colors)
X-12-010- X-12-XRL- X-12-450-	1/2" X 12"	10-Pack 10rls of 10 rls of 450	
X-23-010-BK X-23-XRL-BK X-23-230-BK	7/8" X 23"	10-Pack 10rls of 10 rls of 230	Black Only

Rip-Tie Lite & WrapStrap can be customized with company names and logos.
See page 16 for details.






Rip-Tie WrapStrap - Professional Installers Choice

- WrapStrap is a single strip of double-sided hook and loop fastener that quickly and easily wraps around almost anything.
- You can cut it to any length desired.
- Same features as Rip-Tie Lite.
- WrapStrap is the least expensive of the Rip-Tie light duty cable organizers



CATALOG NUMBER	SIZE	UNIT	COLOR
W-12-1PK- W-12-010- W-12-100-	1/2" X 12"	1-Pack 10-Pack 100-Pack	Black - BK Blue - BU Brown - BN Green - GN Grey - GY Orange - O Red - RD Violet - V White - W Yellow - Y
W-10-1RL- W-60-1SP-	1/2" X 10' 1/2" X 600'	10ft Roll 600ft Roll	
W-75-QRL- W-75-PRL- W-75-1RL- W-75-LRL- W-75-MRL- W-75-HRL- W-75-JRL- W-75-ERL-	1/4" X 75' 3/8" X 75' 1/2" X 75' 5/8" X 75' 3/4" X 75' 1" X 75' 1-1/2" X 75' 2" X 75'	75ft Roll	



Fire Retardant Rip-Tie Lite & WrapStrap

for use in Air handling spaces

- UL (Underwriters Laboratories) 94-V2
- FAR 2.5 853 A/B
- NEC Section 300-22 (C) & (D)

Meeting the requirements of these regulations allow these products to be used for wire and cable management above a hung ceiling or below a raised floor.

Manufactured from Polypropylene and Nylon. It can be refastened 50 times.

CATALOG NUMBER	SIZE	UNIT	COLOR
F-05-010- F-05-XRL- F-05-144-	1/2" X 5"	10-Pack 10rls of 10 1440 Roll	Black - BK Cranberry - CY
F-06-010- F-06-XRL- F-06-120-	1/2" X 6"	10-Pack 10rls of 10 1200 Roll	
F-08-010- F-08-XRL- F-08-900-	1/2" X 8"	10-Pack 10rls of 10 900 Roll	
F-12-010- F-12-XRL- F-12-600-	1/2" X 12"	10-Pack 10rls of 10 600 Roll	
F-18-010- F-18-XRL- F-18-600-	1/2" X 18"	10-Pack 10rls of 10 400 Roll	
G-75-1RL-	1/2" X 75'	75ft Roll	

Rip-Tie Econo Series

*Four Econo Series Cable Organizers
At Budget Prices!!*

- Simple and Easy to Use
- Gentle Hold Hook and Loop
- Sewn, NOT Heat Bonded
- Available in Black

EconoWrap


Econo Series




EconoWrap is designed for organizing cables and cords for the professional and home user. Our economical design features a die cut rounded end to make it a snap to loosen.

CATALOG NUMBER	SIZE	UNIT	COLOR
M-07-E02-BK M-07-E05-BK M-07-E20-BK	3/4" X 7"	2-Pack 5-Pack 20-Pack	Black Only
M-11-E02-BK M-11-E05-BK M-11-E20-BK	3/4" X 11"	2-Pack 5-Pack 20-Pack	

- At least 1000 refastenings.
- Available in 3/4" width, 7" and 11" lengths.
- Can be used to hold simple wire or cable bundles.




EconoCatch



EconoCatch organizes cables against many surfaces. The rubber base adhesive allows for attachment to desks, walls, computers and many other kinds of equipment.


CATALOG NUMBER	SIZE	UNIT	COLOR
B-02-E02-BK B-02-E05-BK B-02-E20-BK	3/4" X 2"	2-Pack 5-Pack 20-Pack	Black Only

- At least 1000 refastenings.
- Rubber based adhesive back is high tack & rapid cure.
- Adheres to most smooth surfaces.




Rip-Tie Econo Series Products can be customized with company names and logos. See page 16 for details.

EconoCinch



EconoCinch has many uses; bundling cables, hoses, and strapping equipment to desks or carts. The loop lock acts like a pulley, giving you leverage to pull the strap as tight as needed. The non-metallic buckle is safe to use around electrical and magnetic equipment.

- At least 1000 refastenings.
- Available in 3/4" width, 12", 18" and 36" lengths.
- Especially useful where an extra tight hold is desired.



CATALOG NUMBER	SIZE	UNIT	COLOR
K-12-E02-BK K-12-E05-BK K-12-E20-BK	3/4" X 12"	2-Pack 5-Pack 20-Pack	Black Only
K-18-E02-BK K-18-E05-BK K-18-E20-BK	3/4" X 18"	2-Pack 5-Pack 20-Pack	
K-36-E02-BK K-36-E05-BK K-36-E20-BK	3/4" X 36"	2-Pack 5-Pack 20-Pack	

EconoCinch-EG



EconoCinch-EG has a solid brass grommet with an ID of 1/4". It can be attached with a metal fastener to walls, carts, equipment racks and van interiors.

- At least 1000 refastenings.
- Available in 3/4" width, 5", 7" and 10" lengths.
- Permanent attachment with solid brass grommet.



CATALOG NUMBER	SIZE	UNIT	COLOR
K-05-GE2-BK K-05-GE5-BK K-05-GET-BK	3/4" X 5"	2-Pack 5-Pack 20-Pack	Black Only
K-07-GE2-BK K-07-GE5-BK K-07-GET-BK	3/4" X 7"	2-Pack 5-Pack 20-Pack	
K-10-GE2-BK K-10-GE5-BK K-10-GET-BK	3/4" X 10"	2-Pack 5-Pack 20-Pack	

Rip-Tie Gecko Tape™

Low, Low Cost

Non-Adhesive, Self-Gripping Tape

Reusable at least 20-25 times



Gecko Tape can be used to bundle Fiber Optic and structured cables INSTEAD of nylon wire ties; in fact, many cable manufactures are recommending "soft-hold" hook and loop ties for use with sensitive data cables. Now **Gecko Tape** makes that switch even easier and more cost efficient.




There are unlimited number of applications: Wire Harness assembly, Medical Tubing, Home Theatre, Audio equipment,

Because it is so inexpensive and weather resistant, it can also be used in Nurseries, Orchards, Vineyards, Tree Farms, Florists, and for Gardening.

CATALOG NUMBER	SIZE	UNIT	COLOR	
G-05-030- G-05-075- G-05-150-	1/2" X 30' 1/2" X 75' 1/2" X 150'	30ft Roll 75ft Roll 150ft Roll	Black - BK	
G-10-030- G-10-075- G-10-150-	1" X 30' 1" X 75' 1" X 150'	30ft Roll 75ft Roll 150ft Roll		Blue - BU Green - GN
G-15-030- G-15-075- G-15-150-	1-1/2" X 30' 1-1/2" X 75' 1-1/2" X 150'	30ft Roll 75ft Roll 150ft Roll		Orange - O Violet - V
G-20-030- G-20-075- G-20-150-	2" X 30' 2" X 75' 2" X 150'	30ft Roll 75ft Roll 150ft Roll	White - W Yellow - Y	
Perforated Gecko Tape				
G-P8-045- G-P8-131- G-P8-225-	1/2" X 8" 1/2" X 8" 1/2" X 8"	45pc Roll 131pc Roll 225pc Roll		

- Available in both continuous and perforated rolls.
- 4 different widths - 1/2" , 1" , 1-1/2" and 2"
- 7 different colors - Black, Blue, Green, Orange, Violet, White, Yellow
- 2" overlap yields 3.0 psi shear strength.



Gecko Tape

Unitag


Cable Identification Done Right It's a Snap!

Unitag cable identification labels were developed to provide a quick, easy method to clearly label virtually any type or size cable or groups of cables.

Unitag cable labels are easy to read. They can be oriented to be easily read in hard to reach areas, behind computer desks and crowded wiring closets. The marking surface can be rotated 360° for easy viewing. Unitag labels are easily installed. They are interchangeable and reusable. A marking pen can be used directly on the surface or a label machine can be used.



CATALOG NUMBER	SIZE	UNIT	COLOR
U-15-010- U-15-050- U-15-100- U-15-1000	5/8" X 1-1/2"	10 Pack 50 Pack 100 Pack 1000 Pack	Blue - BU
U-20-010- U-20-050- U-20-100- U-20-1000	5/8" X 2"	10 Pack 50 Pack 100 Pack 1000 Pack	Orange - O White - W Yellow - Y
U-25-010- U-25-050- U-25-100- U-25-1000	5/8" X 2-1/2"	10 Pack 50 Pack 100 Pack 1000 Pack	



- Quick & easy installation on any cable
- Clearly identifies cables
- Saves time when troubleshooting networks
- UL 94V-2 Fire Retardant
- 3 sizes - 5/8" X 1-1/2", 5/8" X 2", 5/8" X 2-1/2"
- 4 colors - Blue, Orange, White, Yellow

Veltex *Display Fabric*

Veltex Brand Loop laminate fabric is designed for engagement with Velcro Brand Hook fastener.

100% Nylon fabric with Polyester foam core and nylon tricot backing.

Width: 60"
Total Weight: 13 oz per yard

Unitag / Veltex


Hook & Loop

Rip-Tie is one of the largest Hook & Loop distributors in the west.

Rip-Tie has huge stock of hook and loop materials in many colors and sizes.

Standard Back Hook & Loop Materials Hook #88 Loop #1000 Materials - Nylon

Width	Roll Length
3/8"	25 yards
5/8"	50 yards
3/4"	50 yards
1"	50 yards
1-1/2"	50 yards
2"	50 yards
4"	25 yards



Adhesive Backing Hook & Loop Tape Hook #88 Loop #1000 Materials - Acrylic Adhesive #0172

Width	Roll Length
1/4"	25 yards
3/8"	25 yards
1/2"	25 yards
5/8"	25 yards
3/4"	25 yards
1"	25 yards
1-1/2"	25 yards
2"	25 yards
4"	25 yards

Adhesive Back Hook & Loop Dots Hook #88 Loop #1000 Materials - Acrylic Adhesive #0172

Width	Roll Length	Dots Qty per Roll	
3/8"	25 yards	1,880 Dots	72 Dots /yd
1/2"	25 yards	1,440 Dots	57 Dots /yd
5/8"	25 yards	1,200 Dots	48 Dots /yd
3/4"	25 yards	1,050 Dots	42 Dots /yd
7/8"	25 yards	900 Dots	36 Dots /yd
1-3/8"	25 yards	600 Dots	24 Dots /yd
1-7/8"	25 yards	450 Dots	18 Dots /yd

Econo Dots - Hook #711 Loop #3000 Adhesive #0115 *Low Profile with Rubber Adhesive

1/2"	25 yards	1,440	57 /yd
------	----------	-------	--------

Adhesive Back 1"X1" Scored Hook & Loop Hook #88 Loop #1000 Adhesive #0172

Size	Roll Length	Qty per Roll	
1" X 1"	25 yards	900	36 /yd

***Hook & Loop is sold separately**

3M™ Products

Scotchmate™ Industrial Fasteners

Catalog #	Width	Roll Length	Description
3M-3522	1"	50 Yards	Plasticizer Resistant Adhesive Back Hook
3M-3523	1"	50 Yards	Plasticizer Resistant Adhesive Back Loop
3M-3571	1"	50 Yards	VHB High Temp Adhesive Back Hook
3M-3572	1"	50 Yards	VHB High Temp Adhesive Back Loop

VHB = Very High Bond

3M-3522 / 3M-3523

Resists plasticizer migration offering convenient pressure sensitive attachment to many flexible, plasticized vinyl fabrics. Temperature Range -20°F to 120°F Continuous, -20°F to 158°F Intermittent)

Application: Vinyl fabrics, Radar detector to dash, Storage area flaps on boats, Auto/Boat dash accessories, Window sunscreens, Dash covers, Weight Belts, Sports bags, Knee guards, Closure on vinyl boots, Vinyl bags, Vinyl curtains to boat compartments, PVC curtains for refrigerator cases, Vinyl eyeglass cases, Wrist protectors (Archery), etc.


3M-3571 / 3M-3572

Premium Performance. For many static load applications where temperatures may reach 200°F Provides reliable performance over a wide range of temperature and environmental extremes. Temperature Range: -20°F to 200°F Continuous.

Application: Outdoor canvas attachment, Truck tonneau cover, Car bras, auto accessories to dash and windows, Auto carpet, Filter screens for computers, Compartment closure on computers, Control panel on heater, Poly foam lumbar pad in wheelchair, Aircraft insulation blankets, etc.

Dual Lock™ Industrial Fasteners

Catalog #	Width	Roll Length	Description
3M-3460	1"	50 Yards	Type 250 Non-Adhesive Clear
3M-3440	1"	50 Yards	Type 250 Non-Adhesive Black
3M-3550	1"	50 Yards	Type 250VHB P/S White Foam Backing PR
3M-3551	1"	50 Yards	Type 400 VHB P/S White Foam Backing PR
3M-3552	1"	50 Yards	Type 170 VHB P/S White Foam Backing PR
3M-3553	1"	50 Yards	Type 400 VHB P/S Grey Foam Backing
3M-3554	1"	50 Yards	Type 400 VHB P/S Grey Foam Backing
3M-3560-0	1/2"	50 Yards	Type 250 VHB P/S Clear Backing PR
3M-3560-1	1"	50 Yards	Type 250 VHB P/S Clear Backing PR
3M-3560-2	2"	50 Yards	Type 250 VHB P/S Clear Backing PR
3M-3560-4	4"	50 Yards	Type 250 VHB P/S Clear Backing PR
3M-MP-3560	1"	29.4 Feet	Type 250 VHB P/S Clear Backing PR
3M-4570-00	5/8"	25 Yards	Low Profile Dual Lock
3M-4570-01	1"	25 Yards	Low Profile Dual Lock



P/S = Pressure Sensitive
Adhesive Back
VHB = Very High Bond
PR = Plasticizer Resistant

3M-3440 / 3M-3460

Non-Adhesive backing provides for sewing or stapling in place. Self-engaging Type 250 stem pattern (250 mushroom heads per square inch): Only one product to purchase. U.V. resistant. Replaces unsightly mechanical fasteners such as screws, bolts, latches, etc. Temperature Range: -20°F to 200°F Intermittent -20°F to 158°F Continuous

Application: Straps for hanging signs, Closure on scuba dive vest, Foot strap on windsurf board, etc.

3M-3550 / 3M-3551 / 3M-3552

Plasticizer resistant adhesive attachment to many flexible vinyls. Temperature Range: -20°F to 200°F Intermittent -20°F to 158°F Continuous

3M-3553 / 3M-3554

Foam Backing ideal for smooth and slightly irregular surfaces. Temperature Range: -20°F to 200°F Intermittent -20°F to 158°F Continuous

Application: Head light covers, Vandal proof signs, Mount light ballasts, Mount air conditioner cover, Attach nameplate to wall, Beak lights, Sunshade in cars, Access panels, Window louvers, Mount computer battery packs, Decorative wood trim on furniture, Changeable signs, etc.

3M-3560-0 / 3M-3560-1 / 3M-3560-2 / 3M-3560-4

Interlocking mushroom heads for fast, cost-effective reclosable fastening. Excellent tensile strength resulting in replacing unsightly mechanical fasteners (screws, bolts, latches, etc.) in many applications. Self-engaging Type 250 stem pattern: Only one product to purchase. Clear product for color compatibility. U.V. resistance. Plasticizer resistant adhesive attachment to many flexible vinyls. Temperature Range: -20°F to 200°F Intermittent -20°F to 158°F Continuous.

Application: Attach boat covers, Cellular phones, Mount jet ski accessories, Removable tackle box, Traffic signs, Display booth headers, Hold clear acrylic dispensers in place, Secure clear signing panels, Acoustical panels in offices, Accessories on wheelchairs, Awning attachment, etc.

3M