0724 Product Details



0724
(1-1437394-0)
TE Internal Number: 1-1437394-0
Superseded
Search for Replacement Parts

NEMA Terminal Blocks

Not reviewed for RoHS Compliance

Product Highlights:

- 700 Series Block Series
- NEMA Product Line
- Block Type = Dovetail Base
- Contact Configuration = Tubular Screw
- Medium Duty Application

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- None Available

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

Additional Information:
- Product Line Information

Additional Product Images:
- Line Drawing

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Line = NEMA
- Screw Size = 10-32 Slotted Pan Head

Electrical Characteristics:
- Voltage Rating (VAC) = 600
- Amperes (A) = 50.0

Body Features:
- Block Series = 700 Series
- Block Type = Dovetail Base
- Mount Style = Channel Mount (Dovetail Base)
- Wire Range (Solid and Stranded)[MCM] (AWG) = 18-8
- Blown Fuse Indicator = Without
- Blown Fuse Indicator Type = None
- Wire Strip Length (mm [in]) = 8.74 [0.344]

Contact Features:
- Contact Configuration = Tubular Screw
- Pitch (mm [in]) = 9.53 [0.375]

Housing Features:
- Housing Material = Nylon (Painted)

Industry Standards:
- RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance
- Lead Free Solder Processes = Not reviewed for lead free solder process

Operation/Application:
- Application = Medium Duty

Packaging Features:
- Terminals Per Foot = 30

Other:
- Brand = Buchanan

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved | Privacy Policy