Image gallery | 3D view









Part No: 163A19209X

Product Description

- D-SUB Standard
- 9-pos.
- Plug
- Solder pin angled .590"
- Metal bracket
- Quality class 3
- UNC 4-40

Inquiry

General Data | Technical Data | Material Data | Standards | Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<30 N
Extraction force	<30 N
Contact resistance standard	10 mOhm
min. working temperature	-55° C
max. working temperature	+125° C