Image gallery | 3D view









Part No: 6HDD15SAR99E20X

Product Description

- IP67 D-SUB High Density
- 15-pos.
- Socket
- Solder pin straight

Inquiry

General Data | Technical Data | Material Data | Standards | Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP67
Insertion force	50 N
Extraction force	50 N
Contact resistance standard	10 mOhm
min. working temperature	-25° C
max. working temperature	+105° C