


1544545-1 Product Details

 [Live Product Chat](#)




1544545-1

TE Internal Number: 1544545-1

 [Active](#)

 [View 3D PDF](#)

FASTON Uninsulated Receptacles & Housings

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Receptacle
- Tab Fit = 2.79 x 0.50 mm
- Board Mount = No
- Receptacle Style = Straight
- Insulation Support

[View all Features](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [CLIP DE 2.8 A ENFICHAGE DOUX \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version C4\)](#)
- [3D Model \(IGES, Version C4\)](#)
- [3D Model \(STEP, Version C4\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Receptacle
- [Tab Fit \(mm \[in\]\)](#) = 2.79 x 0.50 [.110 x .019]
- [Receptacle Style](#) = Straight
- [Insulation Support](#) = Insulation Support
- [Wire/Cable Type](#) = Regular Wire
- [Insulation Diameter \(mm \[in\]\)](#) = 3.00 [.118]
- [Insertion Force](#) = Low
- [Material](#) = Brass
- [Finish](#) = None
- [Crimp Type](#) = F-Crimp
- CSA Certified = Yes

Mechanical Attachment:

- [Board Mount](#) = No

Body Related Features:

- [Weld Tab](#) = Without
- [Wire Range \(mm \[AWG\]\)](#) = 0.20-1.00² [24-17]
- UL Rating = Listed

Contact Related Features:

- Approved Standards = IEC 760

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- [Packaging Method](#) = Strip
- Packaging Quantity = 15,000

Other:

- [For Hermetic Header Tab](#) = No
- Line = PRONER
- Brand = Tyco Electronics