Datasheet

Art.No. 96.032.4155.7

Male connector with strain relief RST20I3S S1 ZR2 VH GN02

Connector RST20i3, 3 pole, male, screw connection, 250V/20A, for cable diameters 10-14 mm, color of coding: green, color of housing: black

Art.No.	96.032.4155.7
EAN	4015573875111
Order unit	1 pieces

Approvals

Technical data

General

Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Green
Marking of poles	

Connection Data

Connection cross section solid	4 mm²
Connection cross section stranded	4 mm²
Terminations per pole	1

Model

Model	male
Number of poles	3
Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K

Material

Housing material	Polyamide

Halogen free	Yes
Contact material	CuZn
Insulation components continous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	80.4 mm
Width	34.6 mm
Height	34.6 mm

Drawings


A-A
Auslieferungszustand
delivery status
Verpackungseinheit: je 100 Stück
packaging unit: per 100
Type: RST2013S S1 ZR2SVH GN02
96.032.4155.7 01K
STECKERTEIL_MIT_ZUGENTLASTUNG
wieland