


1544291-1 Product Details

[Live Product Chat](#)



1544291-1

TE Internal Number: 1544291-

1

Active

[View 3D PDF](#)

FASTON Uninsulated Receptacles & Housings

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

Product Highlights:

- Receptacle
- Tab Fit = 4.75 x 0.51 mm
- Board Mount = No
- Receptacle Style = Straight
- Insulation Support

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#)

Documentation & Additional Information

Product Drawings:

- [CLIP SECURITE 4.8 A ENFICHAGE DOUX](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Receptacle
- [Tab Fit \(mm \[in\]\)](#) = 4.75 x 0.51 [.187 x .020]
- [Receptacle Style](#) = Straight
- [Insulation Support](#) = Insulation Support
- [Wire/Cable Type](#) = Regular Wire
- [Insulation Diameter \(mm \[in\]\)](#) = 3.80 [.149]
- [Insertion Force](#) = Low
- [Material](#) = Brass
- [Finish](#) = None
- [Crimp Type](#) = F-Crimp
- CSA Certified = Yes

Mechanical Attachment:

- [Board Mount](#) = No

Body Related Features:

- [Weld Tab](#) = Without
- [Wire Range \(mm \[AWG\]\)](#) = 0.50-1.50² [20-15.5]
- UL Rating = Listed

Contact Related Features:

- Approved Standards = IEC 760

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- [Packaging Method](#) = Strip
- Packaging Quantity = 10,000

Other:

- [For Hermetic Header Tab](#) = No
- Line = Microlock
- Brand = Tyco Electronics