



General Information

Kit Part Number:	2110830-3
Description:	Through Hole Right Angle Header and Crimp Receptacle Housing Kit
Application:	Bar Code Scanners, Estimating / Measurement Devices, Instrumentation and Controls, Medical Equipment, Servers / Computers, Vending
Family:	AMPMODU System 50
TE Brand:	AMP Products
Solution:	Off the Board
Product Type:	Wire-to-Board Connectors
Number of Pieces:	116
RoHS:	Yes

Specifications

Circuit Size(s):	4, 8, 15, 20
Current Rating:	1.5A
Flammability Rating:	UL94V-0
Mounting Style:	Through Hole
Orientation:	Right Angle Headers
Pitch:	1.27mm (.050")
Rows:	Single Row
Tool Included:	No
Voltage Rating:	30V
Wire Gauge (AWG):	26-22

Product Highlights

AMPMODU System 50 connector family includes a wide variety of high density board-to-board (through hole and surface mount) and cable-to-board connectors. AMPMODU System 50 is composed of one- and two-row receptacles and post headers on .050" x .100" [1.27mm x 2.54mm] spacing between contacts for extreme density and efficient use of printed circuit board area.

Features and Benefits

- High density contacts spaced on .050" x .100" [1.27mm x 2.54mm] centers
- Single row; select sizes 4-50 positions
- Dual row; select sizes 10-100 positions
- High temperature tolerant thermoplastic housings
- Shrouded and unshrouded headers available in single and dual row, vertical and right angle configurations

Applications

- Medical Equipment
- Instrumentation
- Vending Machines
- Estimating / Measurement Devices
- Bar Code Scanners
- Servers / Computers



Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
5-104186-9	2	15 Circuit Right Angle Unshrouded Header	Datasheet	Details	Search
5-104186-5	2	8 Circuit Right Angle Unshrouded Header	Datasheet	Details	Search
5-104186-1	2	4 Circuit Right Angle Unshrouded Header	Datasheet	Details	Search
487545-1	2	4 Circuit Plain Style Single Row Receptacle Housing	Datasheet	Details	Search
6-104186-1	2	20 Circuit Right Angle Unshrouded Header	Datasheet	Details	Search
1-487547-1-C	100	Flexible Film Contacts	Datasheet	Details	Search
1-487544-7	2	20 Circuit Receptacle	Datasheet	Details	Search
1-487545-2	2	15 Circuit Single Row Receptacle Latching	Datasheet	Details	Search
487544-5	2	8 Circuit Plain Style Single Row Receptacle Housing	Datasheet	Details	Search

Recommended Tool

Part No.	Included in Kit
91572-1	No



