THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2019
© COPYRIGHT 1999 TE Connectivity. All Rights Reserved. ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| | |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | B | REVISED PER EO P17504 | 10DEC2001 | ST | RDR |
| | C | REVISED PER EO P20851 | 25MAR2011 | ST | RDR |
| | C1 | REVISED PER PCN E-19-016328 | 18OCT2019 | JA | IG |
| | C2 | REVISED PER PCN E-21-001566 | 11FEB2021 | MK | IG |







## 3D VIEW

| TE INTERNAL PN | DEUTSCH PN |
|---|---|
| 1027-001-0800 | 1027-001-0800 |
| 1027-002-0800 | 1027-002-0800 |
| 1027-006-0800 | 1027-006-0800 |
| 1027-014-0800 | 1027-014-0800 |

2. ALL PART NUMBERS ARE IN ACCORDANCE WITH RoHS STANDARDS.

1 PART INFORMATION:

| PART NUMBER | MATERIAL | HOLE DIAMETER |
|---|---|---|
| 1027-001-0800 | STAINLESS STEEL | .433 [11.0] |
| 1027-002-0800 | STEEL-ZINC PLATE | .512 [13.0] |
| 1027-006-0800 | STAINLESS STEEL | .512 [13.0] |
| 1027-014-0800 | STEEL-ZINC PLATE | .323 [8.2] |

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 [0.64]
4 PLC ±
ANGLES ±0° 30′0″

MATERIAL 1

FINISH 1

DWN S.THEIS 09NOV1999
CHK B.BYFORD 23MAR2011
APVD S.BEARD 15MAR2011
PRODUCT SPEC
APPLICATION SPEC 114-151009
WEIGHT 10.5g

TE Connectivity

NAME METAL CLIP / MOUNTING BRACKET FOR 8 WAY RECEPTACLE DT SERIES

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A3 | 4AFU8 | C-1027-001/002-006-014-0800 | - |

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV C2

1470-19 (3/11)