Product Families

- Automation
- Hazardous Location
- Industrial Components
- LED Lighting & Signaling
- Machine Safety
- Sensing

HW1M-F2121-22N9
HW 4POS MANT & SPRG MONOLEVER



Add to Cart

Key Features

- Finger safe (IP20) screw terminals standard, other terminal styles available
- All E-Stops meet EN418 (IEC compliant, positive action)
- UL listed, CSA certified, TUV approved, and CE marked
- Super bright incandescent or LED illumination
- UL Type 4X, IP65
- 600V/10A contacts with a wide operating range from 5mA at 3V AC/DC to 10A at 120V AC

Specifications | Literature | Downloads

Operation Type	Spring return
Product Type	Mono lever switch
Mounting Hole Size	Φ22mm
Normally Open Contacts	2
Normally Closed Contacts	2

© 2018 IDEC Corporation All rights reserved. Use of, and copying from, this site is subject to our terms conditions.