


Catalog

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

AMPMODU

↳ .100 Centerline IDC Wire-to-Board (HE 13 - HE 14) Connectors

AMP 281792-4  [Active](#)

**Directive 2002/95/EC
Compliant**

[RoHS Compliant](#)

(Tyco Electronics P/N: 281792-4)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ✦ General Info ✦ Sales Info ✦ Assembly Subcontractors 	<ul style="list-style-type: none"> ✦ Pricing ✦ Product Availability 	<ul style="list-style-type: none"> ✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not relevant for lead free process
Mating Type:	Receptacle
Contact Mating Area Plating:	Tin
No. of Rows:	2
No. of Positions:	8
Terminate To:	Wire
Wire Range (mm [AWG]):	0.08-0.15 ² [28-26]

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Centerline (mm [in]):	2.54 [0.100]
Wire Termination Type:	Insulation Displacement Crimp (IDC)
Contact Material:	Phosphor Bronze
Housing Material:	Glass-Filled PBT
Housing Flammability Rating:	UL 94V-0

Housing Color:	Blue
Packaging Method:	Loose Piece

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)