



5164713-5 Product Details

<p>No Image Available</p>	<p>2.5mm & 5mm Miniature Interconnection System - IDC (Mini-Match)</p>	<p>Quick Links</p> <ul style="list-style-type: none"> ▶ Check Pricing & Availability ▶ Search for Tooling ▶ Product Feature Selector ▶ Contact Us About This Product
<p>5164713-5</p> <p> Active</p>	<p> Always EU RoHS/ELV Compliant (Statement of Compliance)</p> <p>Product Highlights:</p> <ul style="list-style-type: none"> ● Header ● Number of Positions = 5 ● 2.50 mm Centerline ● Terminate To Printed Circuit Board ● PCB Mount Angle = Vertical <p>View all Features</p>	
<p>Documentation & Additional Information</p>		
<p>Product Drawings:</p> <ul style="list-style-type: none"> ● None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> ● None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> ● None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> ● None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> ● None Available <p>CAD Files:</p> <ul style="list-style-type: none"> ● None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> ● Product Line Information <p>Additional Product Images:</p> <ul style="list-style-type: none"> ● PCB Layout <p>Related Products:</p> <ul style="list-style-type: none"> ● Tooling 	
<p>Product Features (Please use the Product Drawing for all design activity)</p>		
<p>Product Type Features:</p> <ul style="list-style-type: none"> ● Product Type = Header ● Number of Positions = 5 ● PCB Mount Angle = Vertical ● Color = Green <p>Body Related Features:</p> <ul style="list-style-type: none"> ● Centerline (mm [in]) = 2.50 [0.098] ● Material Flammability Rating = UL 94V-0 <p>Contact Related Features:</p> <ul style="list-style-type: none"> ● Contact Material = Brass ● Contact Mating Area Plating = Tin 	<p>Housing Related Features:</p> <ul style="list-style-type: none"> ● Housing Material = Thermoplastic Polyester <p>Industry Standards:</p> <ul style="list-style-type: none"> ● RoHS/ELV Compliance = RoHS compliant, ELV compliant ● Lead Free Solder Processes = Wave solder capable to 240°C ● RoHS/ELV Compliance History = Always was RoHS compliant <p>Conditions for Usage:</p> <ul style="list-style-type: none"> ● Terminate To = Printed Circuit Board <p>Other:</p> <ul style="list-style-type: none"> ● Brand = AMP 	

Languages: [English](#) | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Русский](#) | [Italiano](#) | [正體中文 \(繁體\)](#) | [中文 \(簡體\)](#) | [日本語](#)
Country Sites: [China](#) | [Japan](#)

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Supplier](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)
© 2007 Tyco Electronics Corporation All Rights Reserved