


[English](#) [日本語](#)
Electronics
a vital part of your world
**Find
Answers:**

Thursday, 25 August, 2005

CATALOG

 → [Cross Reference](#)
[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

 → [Part Number Search](#)

 → [Document Search](#)

 → [Product Type Search](#)

 → [Product Family Search](#)

 → [Alphabetical Search](#)

 → [RoHS/ELV Compliance & Alternates](#)

 → [CAD Model Search](#)

 → [Brand Search](#)

 → [Tool Search](#)

 → [Multiple Part Comparison](#)

 → [Lead Free Solutions](#)

 → [Help/Glossary](#)
[Home](#)

 e-bulletin newsletter
SUBSCRIBE NOW!
 click here

RF Connectors

 ↳ **SHV**
AMP **51426-5**  Active
(Corporate P/N: 51426-5)
Not ELV or RoHS Compliant
Search for Compliant (RoHS/ELV)
Alternates
CAD Geometry | Search for Parts

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ✦ General Info ✦ Sales Info ✦ Assembly Subcontractors 	<ul style="list-style-type: none"> ✦ Pricing ✦ Product Availability 	<ul style="list-style-type: none"> ✦ Tooling

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Connector
Gender:	Plug
Coaxial Cable Type (RG/U or Mfg.):	59, 59A, 59B, 62, 62A, 62B, 124, 140, 210, Belden 9209, Belden 9269, Belden 9291
Coaxial Cable Termination Type:	Crimp
Body Plating:	Nickel

Other Properties:

Terminate To:	Coaxial Cable
Crimp Type:	Dual
Center Contact Plating:	Gold
Dielectric Material:	TEFLON

Panel Attachment: No

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

