Part Number: 33467-0003

Status: Active

Overview: MX64™ Sealed Single Row Connectors

Description: 2.54mm Pitch MX64™ Terminal, Gold (Au) Plating, 22 AWG, Right Reel Payoff, Also used with MX123™ Female Receptacle Housing



Series

image - Reference only

Documents:

Drawing (PDF)
Product Specification PS-33468-001 (PDF)
Application Specification AS-33468-001 (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	33467
Application	Power
Comments	Right Reel Payoff
Crimp Quality Equipment	Yes
Overview	MX64™ Sealed Single Row Connectors
Product Name	MX123, MX64™
UPC	756054749715

Physical

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	0.225/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.06mm
Wire Size AWG	22
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Application Specification	AS-33468-001
Product Specification	PS-33468-001
Sales Drawing	SD-33468-001

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
33467Series

Use With
MX64™ Sealed Single Row Crimp Housing 31403 , MX123™ Female Receptacle Housing 34566 , 34576

Application Tooling | **FAQ**

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Extraction Tool	0638131400
Hand Crimp Tool	0638114200