This document was generated on 08/04/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0050375093
Status: Active
Overview: SPOX™ Wire-to-Board Connectors
Description: 2.50mm Pitch SPOX™ Wire-to-Board Crimp Housing, without Lock, 9 Circuits



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Product Specification PS-5264-001-001 (PDF)
Packaging Specification SPK-5264-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E29179

General

Product Family	Crimp Housings
Series	5264
Application	Signal, Wire-to-Board
Overview	SPOX™ Wire-to-Board Connectors
Product Name	SPOX™
UPC	800753578395

Physical

Circuits (maximum)	9
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	No
Net Weight	488.900/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Material Info

Engineering Number	5264-09

Reference - Drawing Numbers

Packaging Specification	SPK-5264-001-001
Product Specification	PS-5264-001-001
Sales Drawing	SD-5264-N

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
5264 Series

Mates With
5267 Vertical Shrouded PCB Header
5268 Right Angle Shrouded PCB Header

Use With
5263 2.50mm Pitch SPOX™ Crimp Terminal

This document was generated on 08/04/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION