


[My Cart](#)

[My Part Lists](#)
[Sign In/Register](#)

[English \(Change\)](#)
Have a Question?

Chat with a Product Information Specialist



Japan Update


[Products](#)
[Industries](#)
[Resources](#)
[About TE](#)
[Support Center](#)
[My Account](#)
[Home](#) > [Products](#) > [Card Edge](#) > [Product Feature Selector](#) > Product Details

[Share](#)

[Print](#)

[Email](#)

7-1734774-7 Product Details


7-1734774-7

TE Internal Number: 7-1734774-7

Active
[View 3D PDF](#)

PCI & PCI Express Connectors


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Family Name = PCI Express
- PCB Mounting Orientation = Vertical
- 36 Positions
- Housing Color = Black
- 1.00 mm Centerline

[View all Features](#)
[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [PCI EXPRESS CARD EDGE, V-TYPE, 3GIO.](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version F)
- [3D Model](#) (IGES, Version F)
- [3D Model](#) (STEP, Version F)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- PCB Mounting Orientation = Vertical
- [PCB Mount Style](#) = Through Hole

Termination Features:

- [Termination Post Length \(mm \[in\]\)](#) = 2.30 [0.091]
- Solder Tail Contact Plating = Tin

Body Features:

- Number of Positions = 36
- Centerline (mm [in]) = 1.00 [0.039]
- PCB Mount Retention Type = Pylon
- Ejector = Without

Contact Features:

- Family Name = PCI Express
- [Contact Plating, Mating Area, Material](#) = Gold (15)

Housing Features:

- Housing Color = Black
- Housing Material = PA 46

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Tyco Electronics

- Contact Base Material = Phosphor Bronze

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Sign up for our eNewsletter

 

Follow Us On:



Visit Us On:

