

1059995-1 Product Details

Have a Question?

Chat with a Product Information Specialist



OS-2.9 (2.92mm) RF Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector - RF
- Plug
- Applies To Coaxial Cable
- Coaxial Cable Type (RG/U or Mfg.) = 405 Semi-Rigid/2.16 [.085]
- Coaxial Cable Termination Type = Solder

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

1059995-1

TE Internal Number: 1059995-1

[Active](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [OS-2.9 STRAIGHT CABLE PLUG DIRECT SOLDER ATTACHMENT](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- [OS-2.9 Straight Cable Plug, Direct Solder Attachment...](#) (PDF, English)

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector - RF
- Gender = Plug
- Coupling Nut Material = Stainless Steel
- Coupling Nut Finish = Passivated
- Retaining Ring Material = Beryllium Copper
- Gasket Material = Silicone Rubber

Mechanical Attachment:

- Panel Attachment = Without

Termination Related Features:

- Coaxial Cable Termination Type = Solder

Body Related Features:

- Length (mm [in]) = 11.10 [0.437]
- Support Bead Material = Noryl

Contact Related Features:

- Center Contact Material = Brass
- Center Contact Plating = Gold

Housing Related Features:

- Housing Material = Beryllium Copper
- Housing Finish = Gold Over Nickel

Configuration Related Features:

- Coaxial Cable Type (RG/U or Mfg.) = 405 Semi-Rigid/2.16 [.085]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Hand solderable with tin/lead solder
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Applies To = Coaxial Cable

Other:

- Brand = AMP

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow us on:

