


5145263-3 Product Details

Have a Question?

Chat with a Product Information Specialist



5145263-3

AGP, NLX, Slot 1 Connectors (Standard Edge 1mm)

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- 124 Positions
- Bus Type = AGP (Accelerated Graphic Port)
- Connector Design = Solder Tail
- Termination Post Length = 3.18 mm

[View all Features](#)

TE Internal Number: 5145263-3

[Active](#)

[View 3D PDF](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [ASSEMBLY, 124 POSITION 1mm, CARD EDGE CONNECTOR \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Bus Type](#) = AGP (Accelerated Graphic Port)
- [Connector Design](#) = Solder Tail
- Holddown Material = Brass
- PCB Mount Angle = Vertical
- Comment = Interconnection for AGP technology bringing high performance 3-D graphics and full motion video to the desktop.

Mechanical Attachment:

- Holddown Plating = Tin over Nickel

Termination Related Features:

- [Termination Post Length \(mm \[in\]\)](#) = 3.18 [0.125]
- Solder Tail Contact Plating = Tin over Nickel

Body Related Features:

- [Number of Positions](#) = 124
- Centerline (mm [in]) = 1.00 [0.039]
- Hold-Down Length (mm [in]) = 4.38 [0.172]

Contact Related Features:

- [Contact Plating, Mating Area, Material](#) = Gold (15)
- Contact Base Material = Phosphor Bronze

Housing Related Features:

- Housing Material = Thermoplastic - GF
- Housing Color = Brown

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Tyco Electronics

BOOKMARK

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

