


962952-2 Product Details



962952-2

TE Internal Number: 962952-2

 Active

 [View 3D PDF](#)

1.5/2.5/4.0mm Pin Diameter Connector System

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact
- Product Series = 4.0 mm System
- Contact Type = Socket
- CuNiSi Contact Base Material
- Silver Contact Plating, Mating Area, Material

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [4mm Kontaktbuchse EINZELDICHUNGSSYSTEM \(PDF, German\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version G)
- [3D Model](#) (IGES, Version G)
- [3D Model](#) (STEP, Version G)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- [Product Series](#) = 4.0 mm System
- [Sealed](#) = Yes

Body Features:

- [Wire Range \(mm \[AWG\]\)](#) = 0.50-1.00² [20-17]

Contact Features:

- [Contact Type](#) = Socket
- [Contact Base Material](#) = CuNiSi
- [Contact Plating, Mating Area, Material](#) = Silver

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- [Accepts Wire Insulation Diameter, Range \(mm \[in\]\)](#) = 6.00 [0.236]

Packaging Features:

- [Packaging Method](#) = Reel
- [Packaging Quantity](#) = 1,500

Other:

- [GET 0.64 Connector System](#) = No
- [Brand](#) = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

