


601716-2 Product Details

Share

Print

Email



601716-2

TE Internal Number: 601716-2



Superseded

Search for Replacement Parts

Barrier Strips



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Barrier Strip
- Barrier Style = Double Row, Dual Barrier
- Block Style = Flat
- 11.10 mm Centerline
- Vertical Mount Angle

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Barrier Strip
- [Mount Angle](#) = Vertical
- Screw Material = Brass
- Screw Size = 6-32 x 1/4
- Mounting Ears = With

Mechanical Attachment:

- Screw Plating = Nickel
- Mounting Style = Open End Position

Electrical Characteristics:

- [Top Hardware](#) = Wire Clamp Combo Head
- Number of Levels = Single
- Mounting Insert = Without

Body Features:

- [Barrier Style](#) = Double Row, Dual Barrier
- [Block Style](#) = Flat
- [Centerline \(in \[mm\]\)](#) = 0.4375 [11.10]
- Number of Positions = 2
- Length (mm [in]) = 42.06 [1.656]
- Block Material = Phenolic
- Block Color = Black

Contact Features:

- Mounting Options = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP
- Comment = Other options available upon request, consult our Product Information Center.

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)


Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

