


## 1410480-1 Product Details



1410480-1

TE Internal Number: 1410480-1

[Active](#)

### MULTIGIG RT Connectors and Accessories

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Connector
- Type of Connector = Backplane
- 25.4 mm Card Slot Pitch
- Module Type = Right
- Vertical Mount Angle

[View all Features](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [VERTICAL RECEPTACLE, ASSEMBLY, RIGHT END, FULL, 25.4...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Connector
- Type of Connector = Backplane
- [Mount Angle](#) = Vertical
- Termination Type = Power Combination
- [Series](#) = None

#### Mechanical Attachment:

- [Module Type](#) = Right

#### Termination Features:

- Solder Tail Contact Plating = Tin-Lead over Nickel

#### Body Features:

- Card Slot Pitch (mm [in]) = 25.4 [1]
- Number of Columns = 16
- Mates With = 1410479-1

#### Contact Features:

- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = 1.27 Micro Gold

#### Housing Features:

- Housing Material = Liquid Crystal Polymer (LCP)
- Housing Color = Black
- UL Flammability Rating = UL 94V-0

#### Configuration Features:

- Density = 141 lines/inch

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- Brand = AMP

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

