








DUAL CRIMP TABLE	
PART NO	WIRE SIZE
1326029-9 AND 1-1326029-1	0.35+0.35
	0.35+0.5
	0.35+0.75
	0.35+1.0
	0.5+0.5
1-1326029-0 AND 1-1326029-2	0.5+0.75
	0.35+1.5
	0.5+1.0
	0.5+1.5
	0.75+0.75
	0.75+1.0
	0.75+1.5
	1.0+1.0
	1.0+1.5
	1.0+1.5




DETAIL A
SCALE 20:1

LOC	DIST	REVISIONS					
GE	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G	REVISED PER ECR 05-003800	17NOV2005	DLD	JLT
			G1	REVISED PER ECR 05-017194	23DEC2005	DLD	JLT


1 MATERIAL: 0.30 THICK COPPER ALLOY, PREPLATED WITH 0.0008 MINIMUM THICK MATTE TIN (ELV COMPLIANT).



5. QUALIFICATION OF THE CRIMP APPLICATION TOOLING SHALL BE CONTROLLED BY THE REQUIREMENTS ESTABLISHED UNDER USCAR 21.
6. LOOSE END SPLICING TO BE USED.



SECTION F-F



SECTION G-G

3	1-1326029-0 REELED FOR AMP APPLICATOR						REFERENCE DUAL CRIMP TABLE	1-1326029-2
	1326029-9 REELED FOR AMP APPLICATOR						REFERENCE DUAL CRIMP TABLE	1-1326029-1
2	4.6	1.80	5.35	3.9	1.70	3.88	REFERENCE DUAL CRIMP TABLE	1-1326029-0
	3.6	1.40	4.32	3.3	1.30	2.76	REFERENCE DUAL CRIMP TABLE	1326029-9
3	1326029-4 REELED FOR AMP APPLICATORS						12 AWG	1326029-8
	1326029-3 REELED FOR AMP APPLICATORS						14-16 AWG	1326029-7
	1326029-2 REELED FOR AMP APPLICATORS						18-20 AWG	1326029-6
	1326029-1 REELED FOR AMP APPLICATORS						22 AWG	1326029-5
2	5.2	3.20	4.22	4.7	2.70	5.25	12 AWG	1326029-4
	3.8	1.80	3.16	3.9	1.70	3.88	14-16 AWG	1326029-3
	3.1	1.40	2.55	3.3	1.30	2.76	18-20 AWG	1326029-2
	2.6	1.00	2.04	2.5	0.90	2.11	22 AWG	1326029-1
REELING	L	ØK	J	H	ØF	E	WIRE SIZE	PART NO.

THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE. THE USER OF THIS DRAWING FOR THE PURPOSES OF THE DRAWING SHOULD BE CONTACTED FOR THE LATEST EDITION.		DWN D. STRAUSSER 27APR99	AMP Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK D. BROWN 27APR99	NAME 2.8mm BLADE, UNSEALED	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.10 2 PLC ±0.10 3 PLC ±0.10 4 PLC ±0.10 ANGLES ±4° FINISH		APVD D. BROWN 27APR99	PRODUCT SPEC SAE/USCAR-2 8/97	
MATERIAL		APPLICATION SPEC 114-13013	SIZE A	
		WEIGHT -	CAGE CODE 00779	
		CUSTOMER DRAWING	DRAWING NO 1326029	
		SCALE 10:1	SHEET 1 OF 1	
		REV G1		