Part Number: 09-50-8101

Image not available

Series image - Reference only

Status:	Active - Custom
Series:	41695
Category:	Crimp Housings
Overview:	KK® Interconnection System
Old Part Number:	41695-N-B10

Go to Part Detail▼

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Use With:
KK® Crimp Terminal 2478, 2578, 8818
Trifurcon™ Crimp Terminal 7258, 6438, 6838

Specifications & Other Documents:

Sales Drawings, 3D Models, and Brochures

Documents not available online

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: ELV and RoHS Compliant
China RoHS:
REACH SVHC: Contains SVHC: No
Low-Halogen Status: Not Reviewed

RoHS Certificate of Compliance (PDF)
Multiple Part Product Compliance Form

Part Detail

COLLAPSE ALL

General

Status	**Active - Custom**
Category	Crimp Housings
Series	41695
Application	Power, Wire-to-Board
Overview	KK® Interconnection System
Product Name	KK®
UPC	800754227902

Physical

Breakaway	No
Circuits (maximum)	10
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	3.491/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	0°C to +75°C

Agency Certification

CSA	LR19980
UL	E29179

Material Info

Old Part Number	41695-N-B10

Reference - Drawing Numbers

Packaging Specification	PK-41695-001
Product Specification	PS-08-50
Sales Drawing	SD-41695

Copyright 2012